



Pushing Performance  
Since 1945

# VERSCHRAUBUNG SKV 16



Image is for illustration purposes only. Please refer to product description.

Part number	09 00 000 5167
Specification	VERSCHRAUBUNG SKV 16
HARTING eCatalogue	<a href="https://b2b.harting.com/09000005167">https://b2b.harting.com/09000005167</a>

## Identification

Category	Accessories
Type of accessory	Cable gland
Description of the accessory	With strain relief

## Technical characteristics

Wrench size	24
Degree of protection acc. to IEC 60529	IP68
Size	Pg 16
Width across corners	38 mm

## Material properties

Material (cable glands)	Thermoplastic
Colour (accessories)	RAL 7032 (pebble grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)



**Pushing Performance**  
Since 1945

## Material properties

Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

## Commercial data

Packaging size	10
Net weight	19.25 g
Country of origin	Germany
European customs tariff number	84849000
GTIN	5713140002036
ETIM	EC000441
eCl@ss	27140801 Screwed cable gland (electrical)