

Specification Sheet

Part Number: SRCI0750C2



Co-extruded hinge offers unlimited access to wire and cables and can be open and closed repeatedly without signs of wear.

Rubber based adhesive allows for a permanent bond to most surfaces.

TSR Adhesive Cable Clamp, 1.25" Width, 0.77" Height, PVC, Ivory, 100/pkg

Article Number 151-00279

Type SRCI0750

Color Ivory (IV)

Quantity Per bag

Product Description Manufactured from HellermannTyton's surface raceway, these adhesive cable clamps are designed with a co-extruded hinge offering unlimited and easy access to wire and cable. The clip can be open and closed repeatedly without deformation or signs of wear. The rubber based adhesive allows for a permanent bond to most surfaces. Available in three sizes.

Short Description TSR Adhesive Cable Clamp, 1.25" Width, 0.77" Height, PVC, Ivory, 100/pkg

Global Part Name	SRCI0750-PVC-BGE
Length L (Imperial)	1.25
Length L (Metric)	31.75
Width W (Imperial)	1.36
Width W (Metric)	34.5
Bundle Diameter Max (Imperial)	0.75
Bundle Diameter Max (Metric)	19.0
Height H (Imperial)	.77
Height H (Metric)	19.60
Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
Adhesive	Rubber
Flammability	UL 94 V-0 (excluding adhesive)
UV Resistant (Yes/No)	No
Operating Temperature	+122°F (+50°C)

Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)