



1. 额定值 RATING: 8A 125/250VAC (UL, C-UL)  
12A-8(3)A 250V~ μ T125/55 (ENEC-17, CQC, CB)  
UL APPROVAL FILE NO. :E153399  
ENEC CERTIFICATE NO. :N03691  
CQC CERTIFICATE NO. 10002049682  
CB CERTIFICATE NO. :N056963/A1
2. 功能 FUNCTIONAL: 见电路图 SEE CIRCUIT DESCRIPTION
3. 接触电阻 CONTACT RESISTANCE: <50MΩ
4. 绝缘电阻 INSULATION RESISTANCE: >100MΩ (500VDC BETWEEN OPEN CONTACTS)
5. 耐电压 DIELECTRIC STRENGTH: >1500VAC 0.5 mA 1 MINUTE
6. 所有部件均使用环保材料  
ALL MATERIALS USE IN CONFORMIY WITH THE RoHS DIRECTIVE
7. "○"表示关键尺寸 DENOTES CRITICAL DIMENSIONS



CIRCUIT DIAGRAM



PANEL CUTOUT

NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	TOLERANCE	APPROVED				DESIGN	DRAWN	ALL SIZE ARE IN	MM	DRAWING NO. REV.		
5	→	10	→		DIMENSIONAL TOLERANCES	APPROVED	CHECKED	DESIGN	DRAWN			SCALE	NO			
4	→	9	→		RANGE				LMC		MAT'L	***				
3	→	8	→	X	±0.30				2019.05.20		MATERIAL NO.					
2	→	7	→	X.X	±0.20	<b>LECION ELECTRONIC &amp; HARDWARE CO., LTD.</b>						MFR01-A1F03L1S-B	WIF119038			A
1	→	6	→	X.XX	±0.10											
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'											