

Specification Sheet

Part Number: 151-01310



Fir Tree demonstrates easy insertion with high extraction resistance in 65 +/- 0.4 mm hole
C-clip design allows for multiple uses, from hoses and tubes to harnesses and cables

Dual FT6 Docking Clip, 12-15mm with 6.5mm Fir Tree, PA66HIRHSUV, Black, 2000/pkg

Article Number	151-01310
----------------	-----------

Type	DUALFT6DOCK
------	-------------

Color	Black (BK)
-------	------------

Quantity Per	carton
--------------	--------

Product Description	HellermannTyton connector clips for oval holes are mounted simply by pushing them onto the corresponding clip. The clips provide a wide range of mounting options with anti-rattle and anti-rotation features. The fir tree locks into place when inserted into the hole palpably and ensures a secure fixing at all times. Dual routing clip provides a secure fit for two routings between 12 - 15 mm diameter.
---------------------	---

Short Description	Dual FT6 Docking Clip, 12-15mm with 6.5mm Fir Tree, PA66HIRHSUV, Black, 2000/pkg
-------------------	--

Global Part Name	DUALFT6DOCK-PA66HIRHSUV-BK
------------------	----------------------------

Length L (Imperial)	2.04
---------------------	------

Length L (Metric)	51.8
-------------------	------

Fixation Method	Fir Tree
-----------------	----------

Width W (Imperial)	0.66
--------------------	------

Width W (Metric)	16.66
------------------	-------

Bundle Diameter Min (Metric)	15.5
------------------------------	------

Bundle Diameter Max (Metric)	15.5
------------------------------	------

Height H (Imperial)	1.36
---------------------	------

Height H (Metric)	34.63
-------------------	-------

Nominal Diameter (Metric)	15.5
---------------------------	------

Panel Thickness Min (Imperial)	0.02
--------------------------------	------

Panel Thickness Max (Imperial)	0.24
--------------------------------	------

Panel Thickness Min (Metric)	0.6
------------------------------	-----

Panel Thickness Max (Metric)	6.0
------------------------------	-----

Mounting Hole Diameter D (Imperial)	0.26
-------------------------------------	------

Mounting Hole Diameter D (Metric)	6.5 mm
Mounting Hole Diameter D Max (Metric)	6.9
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin.

