

Specification Sheet

Part Number: 151-02206



Non-rotating fir tree provides easy insertion with high extraction resistance for 8x14 mm and 8x15 mm oval holes.

Meets installation and extraction requirements of SAE/USCAR-2, for easy installation with reliable performance.

Short fir tree avoids obstructions on opposite side of panel.

Connector clip design meets USCAR EWCAP-005-11 clip slot specifications, assuring compliance.

Connector Clip, 8.0–15.0mm Hole Dia., PA66HIRHSUV, Black, 5000/carton

Article Number	151-02206
----------------	-----------

Type	CC16R
------	-------

Color	Black (BK)
-------	------------

Quantity Per	carton
--------------	--------

Product Description	Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.
---------------------	---

Short Description	Connector Clip, 8.0–15.0mm Hole Dia., PA66HIRHSUV, Black, 5000/carton
Global Part Name	CC16R-PA66HIRHSUV-BK
Length L (Imperial)	1.18
Length L (Metric)	30.0
Fixation Method	Fir Tree
Width W (Imperial)	0.72
Width W (Metric)	18.2
Height H (Imperial)	0.92
Height H (Metric)	23.4
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.31
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	3.0
Mounting Hole Diameter D (Imperial)	0.33 " x 0.55 " 0.31 " x 0.59
Mounting Hole Diameter D (Metric)	8.0 x 15.0 mm 8.0 x 14.0 mm
Mounting Hole Diameter D Min (Imperial)	0.31

Mounting Hole Diameter D Max (Imperial) 0.59

Material Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut PA66HIRHSUV

UV Resistant (Yes/No) Yes

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 5000

Package Quantity (Metric) 5000

Customs Number 3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)