

Specification Sheet

Part Number: 156-00551



Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.

Edge Clip provides low insertion force and high extraction force ideal for assembly environments.

2-Piece Cable Tie & Edge Clip, 8.0" Long, EC9, 1–3 mm Panel, 50lb, PA66HS/PA66HIRHSUV, Black, 500/pkg

Article Number	156-00551
----------------	-----------

Type	T50REC9SD
------	-----------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	HellermannTyton's Two Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.
---------------------	--

Short Description	2-Piece Cable Tie & Edge Clip, 8.0" Long, EC9, 1–3 mm Panel, 50lb, PA66HS/PA66HIRHSUV, Black, 500/pkg
-------------------	---

Global Part Name	T50REC9SD-PA66HS/PA66HIRHS-BK
------------------	-------------------------------

Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	8.0
Length L (Metric)	202.0
Fixation Method	EdgeClip, top, assembled, 2 piece
Identification Plate Position	none
Variant	Inside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.20
Bundle Diameter Min (Metric)	5.0
Bundle Diameter Max (Imperial)	2.0
Bundle Diameter Max (Metric)	50.0
Thickness T (Imperial)	0.05
Thickness T (Metric)	1.2
Height H (Imperial)	0.047

Height H (Metric)	1.2
Panel Thickness Min (Imperial)	0.04
Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	3.0
Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS PA66HS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +230°F (-40°C to +110°C) -40°F to +221°F (-40°C to +105°C)
Minimum Extraction Force (Imperial)	50.0
Minimum Extraction Force (Metric)	225
Reach Compliant (Article 33)	No
ROHS Compliant	Yes

Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)