

Specification Sheet

Part Number: 156-02334



Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement. Controlled flex and angled entry promote easy installation. Independent rotation allows for adjustable routing orientation.

MOC Clip to MOC Clip, 10 mm, 10 mm, PA66HIRHSUV, Black, 2000/ctn

Article Number	156-02334
Type	MOC10FMOC10M
Color	Black (BK)
Quantity Per	carton
Product Description	The MOC to MOC is a rotatable dual routing clip that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.
Short Description	MOC Clip to MOC Clip, 10 mm, 10 mm, PA66HIRHSUV, Black, 2000/ctn
Global Part Name	MOC10FMOC10M-PA66HIRHSUV-BK

Length L (Imperial)	1.5
Length L (Metric)	38.1
Variant	Clip to Clip
Bundle Diameter Min (Imperial)	0.37
Bundle Diameter Min (Metric)	9.5
Bundle Diameter Max (Imperial)	0.45
Bundle Diameter Max (Metric)	11.5
Height H (Imperial)	0.77
Height H (Metric)	19.6
Depth D (Imperial)	0.39
Depth D (Metric)	10.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes

UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)