

Specification Sheet

Part Number: 111-01169



Total metal dispersion throughout the tie available in a wide range of sizes

Usable as part of HACCP process

Greatly reduces risk of contamination

Magnetic and X-Ray detectable versions available

Metal Content Tie, 15" Long, 50lb Tensile Strength, PA66MP, Green, 100/pkg

Article Number	111-01169
----------------	-----------

Type	MCT50L
------	--------

Color	Green (GN)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	HellermannTyton's Metal Content Tie is specifically designed for the food, beverage and pharmaceutical processing industries to meet the safety standards set by the Hazardous Analysis of Critical Control Point (HACCP). The tie is nylon-based with metal content dispersed throughout the head and strap allowing any part of the tie to be identified by metal detectors or X-ray inspections, reducing the risk of contamination.
---------------------	---

Short Description	Metal Content Tie, 15" Long, 50lb Tensile Strength, PA66MP, Green, 100/pkg
-------------------	--

Global Part Name	MCT50L-PA66MP-GN
------------------	------------------

Minimum Tensile Strength (Imperial)	50.0
-------------------------------------	------

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	15.0
---------------------	------

Length L (Metric)	380.0
-------------------	-------

Fixation Method	Cable Tie
-----------------	-----------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.19
--------------------	------

Width W (Metric)	4.7
------------------	-----

Bundle Diameter Min (Imperial)	0.06
--------------------------------	------

Bundle Diameter Min (Metric)	1.5
------------------------------	-----

Bundle Diameter Max (Imperial)	4.3
--------------------------------	-----

Bundle Diameter Max (Metric)	110.0
------------------------------	-------

Material	Polyamide 6.6, with metal particles (PA66MP)
Material Shortcut	PA66MP
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

