

SAC-5P-M12MS/ 5,0-520/M12FS VA - Sensor/actuator cable



1564804

<https://www.phoenixcontact.com/us/products/1564804>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 5-position, Plug straight M12, coding: A, on Socket straight M12, coding: A, cable length: 5 m

Commercial data

Item number	1564804
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Sales key	BF03
Product key	BF1CDA
GTIN	4046356308915
Weight per piece (including packing)	272.5 g
Weight per piece (excluding packing)	265.4 g
Customs tariff number	85444290
Country of origin	PL

SAC-5P-M12MS/ 5,0-520/M12FS VA - Sensor/actuator cable



1564804

<https://www.phoenixcontact.com/us/products/1564804>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	5
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Stainless steel

Electrical properties

Contact resistance	$\leq 5 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	No
Status display present	No

Connector

Connection 1

Type	Plug straight M12
Number of positions	5
Coding type	A
Number of positions	5

SAC-5P-M12MS/ 5,0-520/M12FS VA - Sensor/actuator cable



1564804

<https://www.phoenixcontact.com/us/products/1564804>


Connection 2

Type	Socket straight M12
Number of positions	5
Coding type	A
Number of positions	5

Cable/line

Cable length	5 m
--------------	-----

PVC gray 5th conductor gray [520]

Dimensional drawing	
Cable weight	54 kg/km
Number of positions	5
Shielded	no
Cable type	PVC gray 5th conductor gray [520]
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor cross section	0.34 mm²
Wire diameter incl. insulation	1.45 mm ±0.02 mm
External cable diameter	5.9 mm ±0.15 mm
Outer sheath, material	PVC
External sheath, color	gray RAL 7001
Conductor material	Bare Cu litz wires
Material, filler	PVC
Material wire insulation	PVC
Single wire, color	brown, white, blue, black, gray
Thickness, insulation	≥ 0.23 mm (Core insulation) ≥ 0.76 mm (Outer cable sheath)
Overall twist	5 wires around filler to the core
Length of twist, overall twist	55 mm
Max. conductor resistance	max. 58 Ω/km (at 20 °C)
Insulation resistance	≥ 1 GΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Flame resistance	As per UL-Style 2464
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation)

SAC-5P-M12MS/ 5,0-520/M12FS VA - Sensor/actuator cable



1564804

<https://www.phoenixcontact.com/us/products/1564804>

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68
	IP69K
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-25 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)


SAC-5P-M12MS/ 5,0-520/M12FS VA - Sensor/actuator cable

1564804

<https://www.phoenixcontact.com/us/products/1564804>


Drawings

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

Dimensional drawing



Plug, M12 x 1, straight, shielded

SAC-5P-M12MS/ 5,0-520/M12FS VA - Sensor/actuator cable




1564804

<https://www.phoenixcontact.com/us/products/1564804>

Circuit diagram



Dimensional drawing



M12 x 1 socket, straight

SAC-5P-M12MS/ 5,0-520/M12FS VA - Sensor/actuator cable

1564804

<https://www.phoenixcontact.com/us/products/1564804>

Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side

SAC-5P-M12MS/ 5,0-520/M12FS VA - Sensor/actuator cable



1564804

<https://www.phoenixcontact.com/us/products/1564804>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1564804>



UL Listed

Approval ID: FILE E 221474

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	4 A	-	-



cUL Listed

Approval ID: FILE E 221474

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	4 A	-	-

cULus Listed

SAC-5P-M12MS/ 5,0-520/M12FS VA - Sensor/actuator cable



1564804

<https://www.phoenixcontact.com/us/products/1564804>

Classifications

ECLASS

ECLASS-11.0	27060311
ECLASS-12.0	27060311
ECLASS-13.0	27060311

ETIM

ETIM 8.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-5P-M12MS/ 5,0-520/M12FS VA - Sensor/actuator cable



1564804
<https://www.phoenixcontact.com/us/products/1564804>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com