

Heavy-Duty PDU Power Cord, C13 to Right-Angle C14 - 15A, 250V, 14 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: P005-006-14RA











Computer power extension cord with right-angle C14 plug allows connection of a PC, printer or monitor in tight spaces or awkward angles.

Features

C14-to-C13 Power Cable for Network Devices That Require a Heavy-Gauge ConnectionThis IEC-320-C14 to IEC-320-C13 cable features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This C14 male to C13 female cord can be used to connect a computer, server, monitor or drive to a UPS system or PDU or replace or upgrade the standard power cord provided by the device's manufacturer. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

Right-Angle C14 Plug Makes Connecting in Tight Spaces EasierThe C13 to C14 right-angle cable is easier to install in confined spaces, such as the back of a rack enclosure cabinet. When plugged in, the right-angled C14 plug guides the computer power supply cable parallel to your peripheral, allowing you to push the device up against a wall or hide it behind a desk to maximize space.

Highlights

- Right-angle C14 plug allows easier connection in confined or hard-to-reach spaces
- Recommended for powering computers, servers and other network devices
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- PDU-style cord replaces or upgrades standard power cord provided by manufacturer
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

Applications

- Connect devices like computers, servers and monitors to a PDU up to 6-ft. (1.83 m) away in your data center
- Extend an existing power connection up to 6-ft. (1.83 m) to more easily place a device or reach a power source away from your workstation
- Update or replace the standard power cord provided by a device's original manufacturer
- Power a device located in a hard-to-access area behind a desk or flush against a wall

Package Includes

 P005-006-14RA C13 to Right-Angle C14 Power Cable, 6-ft. (1.83 m), Black

Specifications

OVERVIEW		
UPC Code	037332179937	
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; Router; Network Switch; UPS; PDU	
Country/Region	Global	
INPUT		
Maximum Input Amps	15	
Voltage Compatibility (VAC)	100-250	



PHYSICAL		
Plug Color	Black	
Cable Jacket Color	Black	
Cable Jacket Material	PVC	
Cable Jacket Rating	FT2	
Power Cord Jacket Type	SJT	
Cable Outer Diameter (OD)	9.2mm	
Number of Conductors	3	
Wire Gauge (AWG)	14	
Wire Gauge (OD - mm²)	2.08	
Cable Length (ft.)	6	
Cable Length (m)	1.83	
Shipping Dimensions (hwd / in.)	10.00 x 7.00 x 0.10	
Shipping Dimensions (hwd / cm)	25.40 x 17.78 x 0.25	
Shipping Weight (lbs.)	0.66	
Shipping Weight (kg)	0.30	
ENVIRONMENTAL		
Operating Temperature Range	-4° to 140°F (-20° to 60°C)	
Storage Temperature Range	-4° to 140°F (-20° to 60°C)	
Operating Humidity Range	20% to 80% RH	
Storage Humidity Range	20% to 80% RH	
CONNECTIONS		
Side A - Connector 1	IEC-320-C14 - RIGHT ANGLE	
Side B - Connector 1	IEC-320-C13	
FEATURES & SPECIFICATIONS		
Antibacterial	No	
Angled Plug	Yes	
High Voltage	Yes	
Locking Plug	No	
Coiled Power Cord	No	
STANDARDS & COMPLIANCE		
Product Certifications	CSA (Canada); cUL Listed; UL Listed	



Product Compliance	RoHS; REACH	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.