

Specification Sheet

Part Number: 151-14312



Clip includes an internal rib that spans the inside of the bracket to fit securely into the profile of the tubing to prevent lateral movement and slipping of the tubing.

Extended fir tree allows for a wide range of panel thicknesses.

Fir tree design provides low insertion forces and high extraction forces.

Convolute Tubing Clip, 0.5" Max Bundle Diameter, 0.03 - 0.12" Panel Thick, PA66HIRHS, Black, 500/pkg

Article Number	151-14312
----------------	-----------

Type	CTC13FT6
------	----------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	Convolute Tube Clips provide a quick and easy method for firmly securing corrugated covered cables and wires to a surface. Applications such as this can be found in a wide variety of industries such as the wire harness, automotive, trucking, and heavy equipment manufacturing industries.
---------------------	---

Short Description	Convolute Tubing Clip, 0.5" Max Bundle Diameter, 0.03 - 0.12" Panel Thick, PA66HIRHS, Black, 500/pkg
-------------------	--

Global Part Name	CTC13FT6-PA66HIRHS-BK
------------------	-----------------------

Fixation Method	Fir Tree
Variant	Clips
Width W (Imperial)	0.31
Width W (Metric)	8.0
Height H (Imperial)	1.0
Height H (Metric)	25.2
Nominal Diameter (Imperial)	0.5
Nominal Diameter (Metric)	13.0
Panel Thickness Min (Imperial)	0.03
Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	0.75
Panel Thickness Max (Metric)	3.0
Mounting Hole Diameter D (Imperial)	0.26 - 0.28
Mounting Hole Diameter D (Metric)	6.5 - 7.0 mm
Mounting Hole Diameter D Min (Imperial)	0.283
Mounting Hole Diameter D Max (Imperial)	0.275

Mounting Hole Diameter D Max (Metric)	7.0
Disc Diameter (Metric)	16.0
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)