

DVI Y Splitter Cable, Digital and VGA Monitors
 (DVI-I M to DVI-D F and HD15 F) 6-in. (15.24 cm)

MODEL NUMBER: P564-06N-DV



Features

- Splits a DVI-I signal into DVI-D and VGA
- DVI-I Male splits to DVI-D Female and HD15 Female
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p (60Hz)
- Comparable to Wyse 920302-02L and Dell 0X2026

Specifications

OVERVIEW	
UPC Code	037332181534
Product Type	Splitter
Technology	DVI; VGA/SVGA
Host Connector	DVI-I DUAL LINK (MALE)
Cable Type	Passive
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6

Highlights

- Splits a DVI-I signal into DVI-D and VGA
- DVI-I Male splits to DVI-D Female and HD15 Female
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p (60Hz)
- Comparable to Wyse 920302-02L and Dell 0X2026

System Requirements

- A computer with a DVI-I Digital/Analog port
- Simultaneous display of both DVI-D and VGA monitors is not possible with all video cards. Check your computer's video card documentation for compatibility with DVI to DVI + VGA Y splitter cables.

Package Includes

- 6-in. DVI Y Splitter Cable (DVI-I M to DVI-D F and HD15 F)

Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.24
Shipping Weight (kg)	0.11
CONNECTIONS	
Side A - Connector 1	DVI-I DUAL LINK (MALE)
Side B - Connector 1	DVI-D DUAL LINK (FEMALE)
Side B - Connector 2	HD15 (FEMALE)
Latching or Gripping Connector	No
Input x Output	1 x 2
Daisy-chainable / Cascadable	No
FEATURES & SPECIFICATIONS	
MST Support	No
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty