

## Specification Sheet

Part Number: 151-01883



The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters.

|                     |                                                                                                                                                                                           |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 151-01883                                                                                                                                                                                 |
| Type                | BCSFTOVAL                                                                                                                                                                                 |
| Color               | Natural (NA)                                                                                                                                                                              |
| Quantity Per        | carton                                                                                                                                                                                    |
| Product Description | HellermannTyton Bundling Clips are designed to provide simple and easy methods for securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using tape or cable ties. |
| Short Description   | Bundling Clip w/Oval Fir Tree, 2.28" Long, 0.02-0.10" Panel Thickness, PA66HIRHS, Natural, 8000/ctn                                                                                       |
| Global Part Name    | BCSFTOVAL-PA66HIRHS-NA                                                                                                                                                                    |

|                                         |                                                         |
|-----------------------------------------|---------------------------------------------------------|
| Length L (Imperial)                     | 2.28                                                    |
| Length L (Metric)                       | 58.0                                                    |
| Fixation Method                         | Fir Tree for oval holes                                 |
| Width W (Imperial)                      | 0.30                                                    |
| Width W (Metric)                        | 7.62                                                    |
| Height H (Imperial)                     | 0.46                                                    |
| Height H (Metric)                       | 11.6                                                    |
| Panel Thickness Min (Imperial)          | 0.02                                                    |
| Panel Thickness Max (Imperial)          | 0.10                                                    |
| Panel Thickness Min (Metric)            | 0.6                                                     |
| Panel Thickness Max (Metric)            | 2.5                                                     |
| Mounting Hole Diameter D (Imperial)     | 0.24 x 0.48 " 0.25 x 0.50 " 0.25 x 0.50 " 0.27 x 0.47   |
| Mounting Hole Diameter D (Metric)       | 7.0 x 12.0 mm 6.2 x 12.2 mm 6.5 x 13.0 mm 6.5 x 12.5 mm |
| Mounting Hole Diameter D Min (Imperial) | 0.24                                                    |
| Mounting Hole Diameter D Max (Imperial) | 0.51                                                    |
| Mounting Hole Diameter D Max (Metric)   | 13.0                                                    |

|                              |                                                                  |
|------------------------------|------------------------------------------------------------------|
| Material                     | Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) |
| Material Shortcut            | PA66HIRHS                                                        |
| Flammability                 | UL 94 HB                                                         |
| UV Resistant (Yes/No)        | No                                                               |
| Operating Temperature        | -40°F to +230°F (-40°C to +110°C)                                |
| Reach Compliant (Article 33) | Yes                                                              |
| ROHS Compliant               | Yes                                                              |
| Package Quantity (Imperial)  | 8000                                                             |
| Package Quantity (Metric)    | 8000                                                             |
| Customs Number               | 3926909988                                                       |

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).