

Specification Sheet

Part Number: 126-02300



An all-in-one bundling and fixing solution reduces costs.
Disc provides secure insertion and minimizes access of dust, dirt and water.

1-Pc Cable Tie/Arrowhead Mount, 7.0"L, 50lb Tensile, PA66HIRHS, Natural, 1000/pkg

Article Number	126-02300
----------------	-----------

Type	T50SST5
------	---------

Color	Natural (NA)
-------	--------------

Quantity Per	pcs.
--------------	------

Product Description	The Domed Push Mount Tie provides a tight, rattle-free installation and acts as a seal to keep out dust and debris. One-piece mounting ties offer a complete solution by both bundling cable and at the same time providing a mounting solution.
---------------------	--

Short Description	1-Pc Cable Tie/Arrowhead Mount, 7.0"L, 50lb Tensile, PA66HIRHS, Natural, 1000/pkg
-------------------	---

Global Part Name	T50SST5-PA66-NA
------------------	-----------------

Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	225.0
Length L (Imperial)	7.0
Length L (Metric)	170.0
Fixation Method	Arrowhead
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.1
Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	1.2
Bundle Diameter Max (Metric)	31.0
Thickness T (Imperial)	0.05

Thickness T (Metric)	1.2
Height H (Imperial)	0.4
Panel Thickness Min (Imperial)	0.03
Panel Thickness Max (Imperial)	0.06
Panel Thickness Min (Metric)	0.7
Panel Thickness Max (Metric)	1.5
Mounting Hole Diameter D (Imperial)	0.24 - 0.26
Mounting Hole Diameter D (Metric)	6.1 - 6.5 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.26
Mounting Hole Diameter D Max (Metric)	6.5
Disc Diameter (Metric)	16.2
Disc Diameter (Imperial)	0.64

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).