

Specification Sheet

Part Number: 151-01224



Mount and tie combination makes it easy to service bundles in the field
Made from impact modified, heat stabilized, UV resistant material, ideal for heavy duty environments

Eliminates the needs for multiple sized fix diameter clamps

High Torque Mount, 0.375" Mounting Hole Dia, 114.0 lb/ft Max Torque, PA66HIRHSUV, Black, 500/pkg

Article Number	151-01224
----------------	-----------

Type	HDM400
------	--------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	This heavy duty mount, when used with a cable tie eliminates the need to carry multiple sizes of fixed bundle diameter clamps; which reduces inventory and purchasing costs while simplifying the assembly process.
---------------------	---

Short Description	High Torque Mount, 0.375" Mounting Hole Dia, 114.0 lb/ft Max Torque, PA66HIRHSUV, Black, 500/pkg
-------------------	--

Global Part Name	HDM400-PA66HIRHSUV-BK
------------------	-----------------------

Minimum Tensile Strength (Imperial)	120.0
Minimum Tensile Strength (Metric)	533.0
Length L (Imperial)	1.85
Length L (Metric)	47.0
Fixation Method	Screw Mounting and Rivet
Width W (Imperial)	0.98
Width W (Metric)	25.0
Height H (Imperial)	0.81
Height H (Metric)	20.7
Cable Tie Width Max (Imperial)	0.5
Cable Tie Width Max (Metric)	12.7
Mounting Hole Diameter D (Imperial)	0.405
Mounting Hole Diameter D (Metric)	10.29 mm
Mounting Hole Diameter D Min (Imperial)	0.405
Mounting Hole Diameter D Max (Imperial)	0.405
Mounting Hole Diameter D Max (Metric)	10.29

Stud Diameter (Metric)	10.0 mm
Stud Diameter (Imperial)	0.375
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Maximum Torque (kgf-cm)	1576.0
Maximum Torque (lbf-ft)	114.0
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)