

Specification Sheet

Part Number: 156-02512



Capable of holding several cables, depending on cable tie size, for ultimate flexibility.

Zero-insertion-force design requires no tools for quick and easy mounting.

High impact modified, heat-resistant, UV stabilized material is ideal for long-term performance, even in extreme weather.

Cable Tie with Button Mount, 0.35" Hole Dia, 0.12" Max Panel, 0.07" Max Tie Width, PA66HIRHSUV, Black, 500/pkg

Article Number	156-02512
Type	T50RPBM9SET
Color	Black (BK)
Quantity Per	bag
Product Description	This button head mount includes a cable tie to secure cables and wire bundles to panels. Once placed through the panel hole, installers can insert the cable tie through the mount on the panel's opposite surface. The button head mount is designed to fit pre-stamped oval hole sizes from 9x12 mm to 9x14 mm with zero insertion force. Made from impact-modified, heat-resistant, UV stabilized Polyamide 6.6 material, it will withstand extreme environments.
Short Description	Cable Tie with Button Mount, 0.35" Hole Dia, 0.12" Max Panel, 0.07" Max Tie Width, PA66HIRHSUV, Black, 500/pkg

Global Part Name	T50RPBM9SET-PA66HIRHSUV-BK
------------------	----------------------------

Contents of pkg/kit	T50R Cable Tie, Button Mount
---------------------	------------------------------

Minimum Tensile Strength (Imperial)	50.0
-------------------------------------	------

Minimum Tensile Strength (Metric)	225.0
-----------------------------------	-------

Length L (Imperial)	8.0
---------------------	-----

Length L (Metric)	203.2
-------------------	-------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Width W (Imperial)	0.67
--------------------	------

Width W (Metric)	17.0
------------------	------

Bundle Diameter Min (Imperial)	0.16
--------------------------------	------

Bundle Diameter Min (Metric)	4.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.97
--------------------------------	------

Bundle Diameter Max (Metric)	50.0
------------------------------	------

Height H (Imperial)	0.53
---------------------	------

Height H (Metric)	13.40
Panel Thickness Max (Imperial)	0.12
Panel Thickness Max (Metric)	3.0
Mounting Hole Diameter D (Imperial)	0.35 x 0.47 ", 0.35 x 0.55
Mounting Hole Diameter D (Metric)	9.0 x 14.0 mm 9.0 x 12.0 mm
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes

UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)