

Cat5e 350 MHz Snagless Molded (UTP) Ethernet Cable (RJ45 M/M), PoE - Green, 50 ft. (15.24 m)

MODEL NUMBER: N001-050-GN



Features

- Cabling for category 5 (Cat5) and 5e (Cat5e) applications
- Length: 50-ft. color: Green connectors: RJ45 male
- Feature molded connectors with integral strain relief
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation
- PVC 4-pair Solid UTP
- Rated for 350MHz/ 1Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 5e draft 11)
- · Available in other colors and lengths
- Also available without the snagless feature (N002 series)
- Also available Cat6 cables (N201 series)

Specifications

OVERVIEW		
UPC Code	037332172723	
Technology	Cat5/5e	
POWER		
Power Over Cable (PoC) Support	No	
PHYSICAL		

Highlights

- Premium cabling for Category 5 and 5e applications—rated for 350 MHz/1 Gbps communications
- IEEE 802.3ab
- PVC 4-pair Solid UTP
- All cables feature boots with integral strain-relief and RJ45 (Male) connectors

System Requirements

 For 1000Base-T (1Gbps Ethernet), 10/100Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type3 applications.

Package Includes

 50-ft. Green Snagless Cat5e Patch Cable



Green	
PVC	
СМ	
UTP	
5.0 mm	
4 Pair	
Solid Copper	
26 AWG	
50	
15.24	
600	
1524	
10.00 x 0.50 x 8.00	
25.40 x 1.27 x 20.32	
1.23	
0.56	
14° to 104°F (-10° to 40°C)	
5° to 122°F (-15° to 50°C)	
0% to 90% RH, Non-Condensing	
0% to 90% RH, Non-Condensing	
COMMUNICATIONS	
100 MHz	
350 MHz	
1 Gbps (Gigabit)	
802.3ab; 802.3at	
RJ45 (MALE)	
RJ45 (MALE)	
RJ45 (MALE) No	
No	



	1	
Wiring Configuration	EIA/TIA 568B	
Angled Connector	No	
FEATURES & SPECIFICATIONS		
Antibacterial	No	
IP68 Rated	No	
Snagless Connector	No	
IP20 Rated	No	
STANDARDS & COMPLIANCE		
Product Certifications	UL Listed; cUL Listed	
Product Compliance	CE (Europe); RoHS; IEEE 802.3ab 1000Base-T; IEEE 802.3at PoE+; REACH; UKCA	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	



© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.