

Specification Sheet

Part Number: 151-01033



HellermannTyton Connector Clips provide a single method to mount connectors to various surfaces in a variety of applications.

Highly engineered designs feature anti-rattle discs, anti-rotation oval fir trees and clamps for mounting on edges.

An assortment of Connector Cips is available to fit the variety of connector slot designs made by most of the largest global connector manufacturers.

Connector Clip w/Oval Fir Tree, 0.6 - 3.0 mm Panel Thickness, 6.2 - 13.0mm Hole, PA66HIRHSUV, Black, 1000/ctn

Article Number	151-01033
----------------	-----------

Type	CCOVAL6
------	---------

Color	Black (BK)
-------	------------

Quantity Per	carton
--------------	--------

Product Description	Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.
---------------------	---

Short Description	Connector Clip w/Oval Fir Tree, 0.6 - 3.0 mm Panel Thickness, 6.2 - 13.0mm Hole, PA66HIRHSUV, Black, 1000/ctn
-------------------	---

Global Part Name	CCOVAL6-PA66HIRHSUV-BK
Length L (Imperial)	1.16
Length L (Metric)	29.34
Fixation Method	Fir Tree for oval holes
Variant	6.2 x 12.2 mm 6.5 x 12.5 mm 6.5 x 13.0 mm 7.0 x 12.0 mm
Width W (Imperial)	0.69
Width W (Metric)	17.6
Height H (Imperial)	0.60
Height H (Metric)	15.2
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	3.0
Mounting Hole Diameter D (Imperial)	0.24 x 0.48 " 0.25 x 0.50 " 0.25 x 0.50 " 0.27 x 0.47
Mounting Hole Diameter D (Metric)	6.2 x 12.2 mm 7.0 x 12.0 mm 6.5 x 13.0 mm 6.5 x 12.5 mm
Mounting Hole Diameter D Min (Imperial)	0.24

Mounting Hole Diameter D Max (Imperial) 0.51

Mounting Hole Diameter D Max (Metric) 13.0

Material Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut PA66HIRHSUV

Flammability UL 94 HB

Halogen Free Yes

UV Resistant (Yes/No) Yes

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 1000

Package Quantity (Metric) 1000

Customs Number 3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)