

UCT-EMP (60X15) - Snap-in markers



1014119

<https://www.phoenixcontact.com/us/products/1014119>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Snap-in markers, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: insert, lettering field size: 60 x 15 mm, Number of individual labels: 3

Your advantages

- The UCT-EMP... UniCard marking range includes markers for the KMK... marker carriers
- The markers, which are supplied in uniform sheets, can be marked quickly, easily, and precisely using the card printers
- The sheets provide additional space for project information and function text that can be helpful during further assembly
- The multi-section marking strips are easy to fit and can be easily separated if required
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

Commercial data

Item number	1014119
Packing unit	1 pc
Minimum order quantity	10 pc
Sales key	BG10
Product key	BG2318
Catalog page	Page 239 (C-3-2019)
GTIN	4046356783002
Weight per piece (including packing)	8.77 g
Weight per piece (excluding packing)	8.77 g
Customs tariff number	39269097
Country of origin	PL

UCT-EMP (60X15) - Snap-in markers



1014119

<https://www.phoenixcontact.com/us/products/1014119>

Technical data

Product properties

Product type	Device marking
--------------	----------------

Marking

Number of individual labels	3
Number of individual labels per row	1

Mounting

Mounting type	insert
---------------	--------

Material specifications

RoHS compliant	yes
Color	white
Material	PC
Flammability rating according to UL 94	V0
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Components	free from silicone, halogen, and cadmium

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

UCT-EMP (60X15) - Snap-in markers



1014119

<https://www.phoenixcontact.com/us/products/1014119>

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Dimensions

Width	60 mm
Length	15 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Notes

General	Can be labeled via thermal transfer
---------	-------------------------------------

UCT-EMP (60X15) - Snap-in markers



1014119

<https://www.phoenixcontact.com/us/products/1014119>

Classifications

ECLASS

ECLASS-11.0	27281106
ECLASS-12.0	27281106
ECLASS-13.0	27281106

ETIM

ETIM 8.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

UCT-EMP (60X15) - Snap-in markers

1014119

<https://www.phoenixcontact.com/us/products/1014119>



Accessories

TOPMARK NEO - Laser marker

1012015

<https://www.phoenixcontact.com/us/products/1012015>



Laser marking system for the efficient marking of metal or plastic marking material from the LS..., UCT..., UC.../PP..., UM... product families.

TOPMARK LASER - Laser marker

0831831

<https://www.phoenixcontact.com/us/products/0831831>



Laser marker and MARKING NOTEBOOK with German operating system and German keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit

UCT-EMP (60X15) - Snap-in markers

1014119

<https://www.phoenixcontact.com/us/products/1014119>



BLUEMARK ID - Printer

1003334

<https://www.phoenixcontact.com/us/products/1003334>



Monochrome printer with UV LED technology and integrated "MARKING system app" identification software. 7" touch color display for printing plastic tags in UC, UCT, US, and UM format, as well as metal labels.

BLUEMARK ID COLOR - Printer

1002329

<https://www.phoenixcontact.com/us/products/1002329>



CMYK multicolor printer with UV LED technology, with integrated "MARKING system app" identification software, 7" touch color display for printing plastic tags in UC, UCT, and UM format, as well as metal labels.

UCT-EMP (60X15) - Snap-in markers

1014119

<https://www.phoenixcontact.com/us/products/1014119>



BLUEMARK CLED - Printer

5147999

<https://www.phoenixcontact.com/us/products/5147999>



Printers with LED-UV technology for printing plastic labels in UniCard format.

THERMOMARK PRIME - Thermal transfer printer

5148888

<https://www.phoenixcontact.com/us/products/5148888>



Mobile thermal transfer printer for card materials, including power supply unit, Euro/US power cable, and USB cable. User manual printed in German and English. Magazine for UCT-TM... sheets and magazine for US-... cards. One packing unit each UCT-TM 6, US-EMLP (85,6x54), ink ribbon cartridge = 70 m

UCT-EMP (60X15) - Snap-in markers

1014119

<https://www.phoenixcontact.com/us/products/1014119>



THERMOMARK CARD 2.0 - Thermal transfer printer

1085267

<https://www.phoenixcontact.com/us/products/1085267>



Thermal transfer printer for card materials, including Euro/US power cable and USB cable. User manual printed in German and English. Magazine for UCT-TM.. sheets and magazines for US-... cards. One packing unit each UCT-TM 6, US-EMLP (85,6x54), ink ribbon = 50 m

THERMOMARK CARD - Thermal transfer printer

5146464

<https://www.phoenixcontact.com/us/products/5146464>



Thermal transfer printer for cards

UCT-EMP (60X15) - Snap-in markers

1014119

<https://www.phoenixcontact.com/us/products/1014119>



BLUEMARK FLUID-CARTRIDGE - Ink cartridge

5147421

<https://www.phoenixcontact.com/us/products/5147421>

Cartridge, for replacement, 28 ml UV color, black including cleaning cartridge



THERMOMARK-RIBBON 110/50-TC - Ink ribbon

0801384

<https://www.phoenixcontact.com/us/products/0801384>

Ink ribbon, for THERMOMARK CARD for printing product groups UCT..., US..., and UM..., length: 50 m, roll length: 50 m, width: 110 mm, color: black



UCT-EMP (60X15) - Snap-in markers

1014119

<https://www.phoenixcontact.com/us/products/1014119>



BM ID-CARTR. BK - Ink cartridge

1044345

<https://www.phoenixcontact.com/us/products/1044345>



Replacement UV fluid, 23 ml, color: black

BM ID-CARTR. CY - Ink cartridge

1044346

<https://www.phoenixcontact.com/us/products/1044346>



Replacement UV fluid, 23 ml, color: cyan

UCT-EMP (60X15) - Snap-in markers

1014119

<https://www.phoenixcontact.com/us/products/1014119>



BM ID-CARTR. YE - Ink cartridge

1044348

<https://www.phoenixcontact.com/us/products/1044348>




Replacement UV fluid, 23 ml, color: yellow

TOPMARK LASER-MAG UCT-A - Magazine

0803141

<https://www.phoenixcontact.com/us/products/0803141>



Magazine for the TOPMARK LASER, for accommodating UCT material automatically

UCT-EMP (60X15) - Snap-in markers

1014119

<https://www.phoenixcontact.com/us/products/1014119>



TOPMARK LASER-MAG UCT-M - Magazine

0803143

<https://www.phoenixcontact.com/us/products/0803143>

Magazine for the TOPMARK LASER, for accommodating UCT material manually



THERMOMARK-RIBBON 110-TC - Ink ribbon

0801371

<https://www.phoenixcontact.com/us/products/0801371>

Ink ribbon, for THERMOMARK CARD for printing product groups UCT..., US..., and UM..., length: 300 m, roll length: 300 m, width: 110 mm, color: black



UCT-EMP (60X15) - Snap-in markers

1014119

<https://www.phoenixcontact.com/us/products/1014119>



TMP-RIBBON 110 BK 100 - Ink ribbon cartridge

0803374

<https://www.phoenixcontact.com/us/products/0803374>

Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups UCT. ..., US..., and UM..., roll length: 70 m, width: 110 mm, color: black



BLUEMARK CLED-FLUID-CARTR. - Ink cartridge

5146662

<https://www.phoenixcontact.com/us/products/5146662>

Cartridge, for replacement, 20 ml UV color, black, including cleaning cartridge



UCT-EMP (60X15) - Snap-in markers

1014119

<https://www.phoenixcontact.com/us/products/1014119>



KMK HP (60X15) - Cable marker carrier

0830722

<https://www.phoenixcontact.com/us/products/0830722>

Cable marker carrier, transparent, unlabeled, mounting type: Assembly with cable ties, cable diameter: ≥ 9 mm, lettering field size: 60 x 15 mm



KMK UV (60X15) - Cable marker carrier

1014108

<https://www.phoenixcontact.com/us/products/1014108>

Cable marker carrier, transparent, unlabeled, mounting type: Assembly with cable ties, cable diameter: ≥ 9 mm, lettering field size: 60 x 15 mm



UCT-EMP (60X15) - Snap-in markers

1014119

<https://www.phoenixcontact.com/us/products/1014119>



THERMOMARK CARD-UCT-MAG26 - Magazine

0802988

<https://www.phoenixcontact.com/us/products/0802988>

Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets (UCT-EMP...)



TMP-UCT-MAG26 - Magazine

0803370

<https://www.phoenixcontact.com/us/products/0803370>

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EMP (25x6), UCT-EMP (29x8), UCT-EMP (40x17), UCT-EMP (60x15)



UCT-EMP (60X15) - Snap-in markers

1014119

<https://www.phoenixcontact.com/us/products/1014119>



TOPMARK LASER DE CH - Laser marker

0803285

<https://www.phoenixcontact.com/us/products/0803285>



Laser marker and MARKING NOTEBOOK with German operating system and German keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit

TOPMARK LASER RU RU - Laser marker

0803286

<https://www.phoenixcontact.com/us/products/0803286>



Laser marker and MARKING NOTEBOOK with Russian operating system and Russian keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit.

UCT-EMP (60X15) - Snap-in markers

1014119

<https://www.phoenixcontact.com/us/products/1014119>



TOPMARK LASER SE SE - Laser marker

0803287

<https://www.phoenixcontact.com/us/products/0803287>



Laser marker and MARKING NOTEBOOK with Swedish operating system and Swedish keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit.

TOPMARK LASER DK DK - Laser marker

0803288

<https://www.phoenixcontact.com/us/products/0803288>



Laser marker and MARKING NOTEBOOK with Danish operating system and Danish keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit

UCT-EMP (60X15) - Snap-in markers

1014119

<https://www.phoenixcontact.com/us/products/1014119>



TOPMARK LASER CN US - Laser marker

0803289

<https://www.phoenixcontact.com/us/products/0803289>



Laser marker and MARKING NOTEBOOK with Chinese operating system and American keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit

TOPMARK LASER PL US - Laser marker

0803290

<https://www.phoenixcontact.com/us/products/0803290>



Laser marker and MARKING NOTEBOOK with Polish operating system and American keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit

UCT-EMP (60X15) - Snap-in markers

1014119

<https://www.phoenixcontact.com/us/products/1014119>



TOPMARK LASER FR FR - Laser marker

0803291

<https://www.phoenixcontact.com/us/products/0803291>



Laser marker and MARKING NOTEBOOK with French operating system and French keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit

TOPMARK LASER IT IT - Laser marker

0803292

<https://www.phoenixcontact.com/us/products/0803292>



Laser marker and MARKING NOTEBOOK with Italian operating system and Italian keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit

UCT-EMP (60X15) - Snap-in markers

1014119

<https://www.phoenixcontact.com/us/products/1014119>



TOPMARK LASER ES ES - Laser marker

0803293

<https://www.phoenixcontact.com/us/products/0803293>



Laser marker and MARKING NOTEBOOK with Spanish operating system and Spanish keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit

TOPMARK LASER PT PT - Laser marker

0803295

<https://www.phoenixcontact.com/us/products/0803295>



Laser marker and MARKING NOTEBOOK with Portuguese operating system and Portuguese keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit

UCT-EMP (60X15) - Snap-in markers

1014119

<https://www.phoenixcontact.com/us/products/1014119>



TOPMARK LASER US - Laser marker

0803297

<https://www.phoenixcontact.com/us/products/0803297>



Laser marker and MARKING NOTEBOOK with English operating system and English keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 120 V extraction unit

TOPMARK LASER HU HU - Laser marker

0803299

<https://www.phoenixcontact.com/us/products/0803299>



Laser marker and MARKING NOTEBOOK with Hungarian operating system and Hungarian keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit

UCT-EMP (60X15) - Snap-in markers

1014119

<https://www.phoenixcontact.com/us/products/1014119>



BM ID-MAG20 - Magazine

1044356

<https://www.phoenixcontact.com/us/products/1044356>

Infeed magazine for accommodating a max. of 20 UniCard sheets



BM ID-MAG40 - Magazine

1044357

<https://www.phoenixcontact.com/us/products/1044357>

Infeed magazine for accommodating a maxi. of 40 UniCard sheets



Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com