

Stainless Steel Hose Clamp

Features

- Stainless Steel for high reliability
- Wide Adjustment Range 12" to 2"
- Worm Gear with 5/16" Slotted Drive
- Heavy Duty: 0.024" Thick Band, 9/16" Width
- Meets SAEJ1508 Specification



Applications

- Antenna Mounting
 - Marine Applications
- Enclosure Mounting
 - Farm Applications

Description

The 5700052 worm gear drive hose clamps are a heavy duty stainless steel hose clamp. The wide adjustment range from 12" to 2" allow for one hose clamp to be used in a wide variety of applications. Installers and mechanics only need to stock one hose clamp and always have the correct hose clamp for the job at hand. The quick release feature enables faster installs.

Specifications

| | 5700052 |
|-------------------------------|--|
| Materials | Band: SUS304 Stainless ; Worm Gear: Plated Steel |
| Adjustment Range | 2" to 12" |
| Worm Gear Drive | 5/16" Slotted Hex Drive |
| Band Width | 9/16" (0.56") |
| Band Thickness | 0.024" |
| Max Recommended Torque | 50 inlbs |
| Standards | SAEJ1508 |
| Weight | 3 oz |
| Warranty | 3 years |



Lock Position



Release Position

Ordering:

5700052 2" to 12" Worm Gear Stainless Hose Clamp with Quick Release

For further information contact:

Tyconsystems.com

