

GlobTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: European Plug CEE 7/7, IP44, Splash Proof to Stripped and Tinned ROJ 120±5 mm, RIJ 6±1 mm, GT Cable #447: 1.0 mm ² / 3 Conductors, 7.0±0.2mm OD, H05RR-F, 70 Deg.C, 500V, BLU/BRN/GRN-YW, Approvals: , 3200±50mm, GlobTek Black		
	Model No. Power Cord		
	<table border="1"> <tr> <td data-bbox="308 203 1689 295">Part No./Ordering No. 23144473M200</td><td data-bbox="1689 203 1915 295">Rev B</td></tr> </table>	Part No./Ordering No. 23144473M200	Rev B
Part No./Ordering No. 23144473M200	Rev B		

CUSTOMIZED LENGTHS, COLORS, CABLE TYPES, TERMINATIONS/PLUGS/RECEPTACLES AVAILABLE UPON REQUEST. ADDITIONAL PLUG OPTIONS ARE AVAILABLE AT <https://www.globtek.com/connectors/> STANDARD PLUGS AND CONNECTORS CAN BE SEEN ONLINE AT <https://www.globtek.com/connectors/> ACTUAL CONNECTORS, OVERMOLDS, FERRITES MAY VARY SLIGHTLY FROM THE PICTURE BELOW DIMENSIONS ARE IN MM UNLESS SPECIFIED OTHERWISE

In Addition to GlobTek Inc.'s renewed ISO9001:2008 - Quality Management System Certification, GlobTek Inc. is now certified to:

ISO13485:2003 - Medical Devices Quality Management System Certification
ISO14001:2004 - Environmental Management System Certification

ISO Certificates are available online at <https://www.globtek.com/iso-certificates/>
Prop 65 Statement: <https://en.globtek.com/prop-65-statement.pdf>

The acceptance of this specification and use of the product described in this document indicates the acceptance and binding of the customer to Globtek TERMS AND CONDITIONS (attached to the end of this document), which supersede all other agreements, terms, and conditions (<https://en.globtek.com/terms-and-conditions/>).

The purchaser of this product (Customer) agrees that it is their sole responsibility to determine suitability/fitness of the product described in this specification for their application and to take precautions for protection against any hazards attendant to the handling and use of the product.

Footnote:

GlobTek Inc. will not be liable for the safety and performance of these power supplies if unauthorized access and repair occurs. End user should consult applicable UL, CSA or EN standards for proper installation instruction.

Limitation of Use:

GlobTek products are intended for use with commercial, medical, and/or industrial equipment only. GlobTek product are not authorized for use as mission critical components in life support hazardous environment, nuclear or aircraft applications without prior written approval from the CEO of GlobTek Inc.
Contents of this document are subject to change without prior notice.

Customer Approval of Specification:

Please approve, sign and send back to GlobTek so we can complete order processing.
A delay in receipt of this form will delay delivery schedule.

Company Name:	Customer P/N:
Quote Number:	Date:
Authorized Representative Name:	Authorized Representative Signature:

GlobTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: European Plug CEE 7/7, IP44, Splash Proof to Stripped and Tinned ROJ 120±5 mm, RIJ 6±1 mm, GT Cable #447: 1.0 mm² / 3 Conductors, 7.0±0.2mm OD, H05RR-F, 70 Deg.C, 500V, BLU/BRN/GRN-YW, Approvals: , 3200±50mm, GlobTek Black		
	Model No. Power Cord		
	Part No./Ordering No. 23144473M200		Rev B

CUSTOMIZED LENGTHS, COLORS, CABLE TYPES, TERMINATIONS/PLUGS/RECEPTACLES AVAILABLE UPON REQUEST. ADDITIONAL PLUG OPTIONS ARE AVAILABLE AT <https://www.globtek.com/connectors/> STANDARD PLUGS AND CONNECTORS CAN BE SEEN ONLINE AT <https://www.globtek.com/connectors/> ACTUAL CONNECTORS, OVERMOLDS, FERRITES MAY VARY SLIGHTLY FROM THE PICTURE BELOW DIMENSIONS ARE IN MM UNLESS SPECIFIED OTHERWISE

REVISION HISTORY

REV	DESCRIPTION	SUB	DATE	APPROVED
B	Update to SF format	QA	07/08/2022	QA
A	Initial release	QA	08/16/2017	QA

Cordset Information:

CordsetColor:GlobTek Black

Cord Length (mm):3200±50

NOTES:

PROPRIETARY INFORMATION


PROPRIETARY OF GLOBTEK, INC. ANY REPRODUCTION, DISCLOSURE OR USE OF THIS DRAWING, IN WHOLE OR IN PART, IS HEREBY PROHIBITED EXCEPT AS SPECIFIED IN WRITING BY GLOBTEK, INC. © GlobTek, Inc.

2011 - 2023

quest /09/21/2023 3:41:25 PM

GlobTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: European Plug CEE 7/7, IP44, Splash Proof to Stripped and Tinned ROJ 120±5 mm, RIJ 6±1 mm, GT Cable #447: 1.0 mm² / 3 Conductors, 7.0±0.2mm OD, H05RR-F, 70 Deg.C, 500V, BLU/BRN/GRN-YW, Approvals: , 3200±50mm, GlobTek Black	
	Model No. Power Cord	
	Part No./Ordering No. 23144473M200	Rev B


CUSTOMIZED LENGTHS, COLORS, CABLE TYPES, TERMINATIONS/PLUGS/RECEPTACLES AVAILABLE UPON REQUEST. ADDITIONAL PLUG OPTIONS ARE AVAILABLE AT <https://www.globtek.com/connectors/> STANDARD PLUGS AND CONNECTORS CAN BE SEEN ONLINE AT <https://www.globtek.com/connectors/> ACTUAL CONNECTORS, OVERMOLDS, FERRITES MAY VARY SLIGHTLY FROM THE PICTURE BELOW DIMENSIONS ARE IN MM UNLESS SPECIFIED OTHERWISE



GlobTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: European Plug CEE 7/7, IP44, Splash Proof to Stripped and Tinned ROJ 120±5 mm, RIJ 6±1 mm, GT Cable #447: 1.0 mm² / 3 Conductors, 7.0±0.2mm OD, H05RR-F, 70 Deg.C, 500V, BLU/BRN/GRN-YW, Approvals: , 3200±50mm, GlobTek Black	
	Model No. Power Cord	
	Part No./Ordering No. 23144473M200	Rev B

CUSTOMIZED LENGTHS, COLORS, CABLE TYPES, TERMINATIONS/PLUGS/RECEPTACLES AVAILABLE UPON REQUEST. ADDITIONAL PLUG OPTIONS ARE AVAILABLE AT <https://www.globtek.com/connectors/> STANDARD PLUGS AND CONNECTORS CAN BE SEEN ONLINE AT <https://www.globtek.com/connectors/> ACTUAL CONNECTORS, OVERMOLDS, FERRITES MAY VARY SLIGHTLY FROM THE PICTURE BELOW DIMENSIONS ARE IN MM UNLESS SPECIFIED OTHERWISE

CABLE IMAGE



PROPRIETARY INFORMATION

PROPRIETARY OF GLOBTEK, INC. ANY REPRODUCTION, DISCLOSURE OR USE OF THIS DRAWING, IN WHOLE OR IN PART, IS HEREBY PROHIBITED EXCEPT AS SPECIFIED IN WRITING BY GLOBTEK, INC. © GlobTek, Inc.

2011 - 2023

quest /09/21/2023 3:41:25 PM

GlobTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: European Plug CEE 7/7, IP44, Splash Proof to Stripped and Tinned ROJ 120±5 mm, RIJ 6±1 mm, GT Cable #447: 1.0 mm ² / 3 Conductors, 7.0±0.2mm OD, H05RR-F, 70 Deg.C, 500V, BLU/BRN/GRN-YW, Approvals: , 3200±50mm, GlobTek Black	
	Model No. Power Cord	Rev B

CUSTOMIZED LENGTHS, COLORS, CABLE TYPES, TERMINATIONS/PLUGS/RECEPTACLES AVAILABLE UPON REQUEST. ADDITIONAL PLUG OPTIONS ARE AVAILABLE AT <https://www.globtek.com/connectors/> STANDARD PLUGS AND CONNECTORS CAN BE SEEN ONLINE AT <https://www.globtek.com/connectors/> ACTUAL CONNECTORS, OVERMOLDS, FERRITES MAY VARY SLIGHTLY FROM THE PICTURE BELOW DIMENSIONS ARE IN MM UNLESS SPECIFIED OTHERWISE

End A Code:2314-1, type IP44 Description:European Plug CEE 7/7, IP44, Splash Proof Rating (V):250 Rating (A):16.0 Gender:Male Overmolded:Yes	Cable Code:447 Description:GT Cable #447: 1.0 mm ² / 3 Conductors, 7.0±0.2mm OD, H05RR-F, 70 Deg.C, 500V, BLU/BRN/GRN-YW, Approvals: Color:GlobTek Black Wire Gauge(AWG):1.0 mm ² Cond:3 Type:H05RR-F Temperature:70° C Amps:10 Volts:500 OD:7.0±0.2 ConductorsColors:BLU/BRN/GRN-YW	End B Code:A00-120 Description:Stripped and Tinned ROJ 120±5 mm, RIJ 6±1 mm Rating (V): Rating (A): Gender:N/A Overmolded:No
----------------------------------------------------------------------------------------------------------------------------------------------------------------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	------------------------------------------------------------------------------------------------------------------------------------------------

Overall cable rating:

Plug Approvals	Cable Approvals	Connector Approvals
----------------	-----------------	---------------------



KEMA (Keuring van Elektrotechnische Materialen te Arnhem) /Dekra (Netherlands Certification)



VDE

IEMMEQU<HAR>

AGENCY ONLINE DOCUMENTS	http://en.globtek.com/cordsets/
RoHS/RoHS3 Declaration	https://www.globtek.com/pdf/rohs_cert/01t30000002oxk0AAA
REACH Declaration	https://www.globtek.com/pdf/iso_certificates/REACH.pdf
Conflict Minerals Declaration	https://www.globtek.com/pdf/conflict-minerals.pdf
Prop 65 Statement	https://en.globtek.com/prop-65-statement.pdf
CE.UKCA.Cord	https://globtek.secure.force.com/spec/ec_decl_product_model_family_incl_cord?id=01t30000002oxk0

PROPRIETARY INFORMATION

PROPRIETARY OF GLOBTEK, INC. ANY REPRODUCTION, DISCLOSURE OR USE OF THIS DRAWING, IN WHOLE OR IN PART, IS HEREBY PROHIBITED EXCEPT AS SPECIFIED IN WRITING BY GLOBTEK, INC. © GlobTek, Inc. 2011 - 2023

quest /09/21/2023 3:41:25 PM

GlobTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: European Plug CEE 7/7, IP44, Splash Proof to Stripped and Tinned ROJ 120±5 mm, RIJ 6±1 mm, GT Cable #447: 1.0 mm² / 3 Conductors, 7.0±0.2mm OD, H05RR-F, 70 Deg.C, 500V, BLU/BRN/GRN-YW, Approvals: , 3200±50mm, GlobTek Black	
	Model No. Power Cord	
	Part No./Ordering No. 23144473M200	Rev B


CUSTOMIZED LENGTHS, COLORS, CABLE TYPES, TERMINATIONS/PLUGS/RECEPTACLES AVAILABLE UPON REQUEST. ADDITIONAL PLUG OPTIONS ARE AVAILABLE AT <https://www.globtek.com/connectors/> STANDARD PLUGS AND CONNECTORS CAN BE SEEN ONLINE AT <https://www.globtek.com/connectors/> ACTUAL CONNECTORS, OVERMOLDS, FERRITES MAY VARY SLIGHTLY FROM THE PICTURE BELOW DIMENSIONS ARE IN MM UNLESS SPECIFIED OTHERWISE

IPXY rating is based on 3rd party testing and customers should check suitability and test system level IPXY rating before ordering.

GlobTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: European Plug CEE 7/7, IP44, Splash Proof to Stripped and Tinned ROJ 120±5 mm, RIJ 6±1 mm, GT Cable #447: 1.0 mm² / 3 Conductors, 7.0±0.2mm OD, H05RR-F, 70 Deg.C, 500V, BLU/BRN/GRN-YW, Approvals: , 3200±50mm, GlobTek Black	
	Model No. Power Cord	
	Part No./Ordering No. 23144473M200	Rev B

CUSTOMIZED LENGTHS, COLORS, CABLE TYPES, TERMINATIONS/PLUGS/RECEPTACLES AVAILABLE UPON REQUEST. ADDITIONAL PLUG OPTIONS ARE AVAILABLE AT <https://www.globtek.com/connectors/> STANDARD PLUGS AND CONNECTORS CAN BE SEEN ONLINE AT <https://www.globtek.com/connectors/> ACTUAL CONNECTORS, OVERMOLDS, FERRITES MAY VARY SLIGHTLY FROM THE PICTURE BELOW DIMENSIONS ARE IN MM UNLESS SPECIFIED OTHERWISE

Hanking:231-00
Description:250 +/-50mm
Image:



Notes/Modifications/Customizations (notes in this section supersede the values shown in the standard spec):