

Specification Sheet

Part Number: 170-03032



HellermannTyton braided sleeving installation tools are designed to accommodate a wide variety of braided sleeving products. Tools are designed and built durable to withstand production environments. Tools are available in both benchmount and handheld for all kinds of use.

Braided Sleeving, Installation Tool, 1/2" Split Wrap, 1/pkg

Article Number	170-03032
----------------	-----------

Type	BSWTOOL12
------	-----------

Color	Orange (OG)
-------	-------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton offers a wide variety of application tools to assist in the installation of braided sleeving. These application tools are available in both bench mount and handheld styles.
---------------------	--

Short Description	Braided Sleeving, Installation Tool, 1/2" Split Wrap, 1/pkg
-------------------	---

Global Part Name	BSWTOOL12-PL-OG
------------------	-----------------

Bundle Diameter Max (Imperial)	0.5
Bundle Diameter Max (Metric)	12.7
Diameter D (Imperial)	0.50
Diameter D (Metric)	12.7
Nominal Diameter (Imperial)	0.5
Nominal Diameter (Metric)	12.7
Material	Plastic (PL)
Material Shortcut	PL
Halogen Free	Yes
UV Resistant (Yes/No)	No
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8205599000

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)