



Product: [8908](#)

Lead Wire, #8 Str TC, PVC Ins, AWM 1028 AWM 1015 AWM 1231

Request Sample

Product Description

Low Temp Plastic Lead Wire, 8AWG (133x29) Tinned Copper, PVC Insulation, AWM 1028 AWM 1015 AWM 1231 CSA TYPE TEW 600V 105C

Technical Specifications

Product Overview

Suitable Applications:	inter-connection circuits, internal wiring of computer and electronic equipments, internal wiring of appliances, machine tool wire
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	1	8	133x29	TC - Tinned Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter
PVC - Polyvinyl Chloride	0.048 in (1.2 mm)	0.262 in (6.65 mm)

Overall Cable Diameter (Nominal):	0.262 in (6.65 mm)
-----------------------------------	--------------------

Electrical Characteristics

Voltage

UL Voltage Rating
600 V RMS

Mechanical Characteristics

Temperature

UL Temperature
105°C

Bend Radius

Stationary Min.	Installation Min.
1.05 in (26.7 mm)	1.05 in (26.7 mm)

Max. Pull Tension:	213 lbs (96.6 kg)
Bulk Cable Weight:	74 lbs/1000ft

Standards and Compliance

Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	VW-1
NEC / UL Compliance:	Article 310, MTW or TW
AWM Compliance:	AWM 1015, AWM 1028, AWM 1231, CSA AWM I A/B
CEC / C(UL) Compliance:	TEW
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

History

Update and Revision:	Revision Number: 0.448 Revision Date: 01-20-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8908 010250	Black	Reel	250 ft	612825217992	C
8908 0101500	Black	Reel	1,500 m	612825217985	
8908 013250	Blue, Dark	Reel	250 ft	612825218005	
8908 001250	Brown	Reel	250 ft	612825217831	
8908 0081500	Gray	Reel	1,500 m	612825217930	
8908 005250	Green, Dark	Reel	250 ft	612825217916	C
8908 002250	Red	Reel	250 ft	612825217886	
8908 0071500	Violet	Reel	1,500 m	612825217923	
8908 004250	Yellow	Reel	250 ft	612825217909	
8908 0041500	Yellow	Reel	1,500 m	612825217893	

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.