

# PDU Power Cord, C13 to C14 - 10A, 250V, 18 AWG, 2 ft. (0.61 m), White

MODEL NUMBER: P004-002-AWH











Computer power extension cord connects 2 devices with C13/C14 power connectors or extends your existing power connection by 2 ft.

#### **Features**

C14-to-C13 Power Cable Connects Computers, Printers, Servers and Other EquipmentThis IEC-320-C14 to IEC-320-C13 cable is designed for small data center, office workstation and other lower-amp applications. This C14 male to C13 female cord can be used to power a computer, server or monitor; attach a server or drive to a UPS system or PDU; or extend an existing connection up to 2-ft. (0.61 m). The 2-ft. (0.61 m) length helps reduce cable clutter and minimize the risk of tripping.

Color-Coded to Avoid Misidentification That Can Cause Costly DowntimeThis computer power extension cord features a white SJT jacket and fully molded white ends. The color-coding allows easy, fast identification in a crowded rack or workstation and helps prevent the cable from becoming inadvertently disconnected.

### **Highlights**

- Recommended for powering computers, printers and other essential peripherals
- Adds 2-ft. (0.61 m) to your existing connection to provide more flexibility in placing devices
- C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable
- Color-coded white for fast, easy identification in a crowded rack or workstation

#### **Applications**

- Connect devices like computers, servers and monitors to a PDU up to 2-ft. (0.61 m) away in your data center
- Extend an existing power connection up to 2-ft. (0.61 m) to more easily place a device or reach a power source near your workstation
- Provide a high-quality replacement for a worn-out or missing power cord

#### **Package Includes**

 P004-002-AWH C14 Male to C13 Female Power Cable, 2-ft. (0.61 m), White

## **Specifications**

OVERVIEW		
UPC Code	037332198884	
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU	
Country/Region	Global	
INPUT		
Maximum Input Amps	10	
Voltage Compatibility (VAC)	100-250	
PHYSICAL		



Plan Oales	NATI-Y-	
Plug Color	White	
Cable Jacket Color	White	
Cable Jacket Material	PVC	
Cable Jacket Rating	FT2	
Power Cord Jacket Type	SJT	
Cable Outer Diameter (OD)	7.7mm	
Number of Conductors	3	
Wire Gauge (AWG)	18	
Wire Gauge (OD - mm²)	0.82	
Cable Length (ft.)	2	
Cable Length (m)	0.61	
Cable Length (cm)	60.96	
Shipping Dimensions (hwd / in.)	0.50 x 7.50 x 8.40	
Shipping Dimensions (hwd / cm)	1.27 x 19.05 x 21.34	
Shipping Weight (lbs.)	0.40	
Shipping Weight (kg)	0.18	
ENVIRONMENTAL		
Operating Temperature Range	-4° to 140°F (-20° to 60°C)	
Storage Temperature Range	-4° to 140°F (-20° to 60°C)	
Operating Humidity Range	20% to 80% RH	
Storage Humidity Range	20% to 80% RH	
CONNECTIONS		
Side A - Connector 1	IEC-320-C14	
Side B - Connector 1	IEC-320-C13	
FEATURES & SPECIFICATIONS		
Antibacterial	No	
Angled Plug	No	
High Voltage	Yes	
Locking Plug	No	
Coiled Power Cord	No	
STANDARDS & COMPLIANCE		
Product Certifications	CSA (Canada); cUL Listed; UL Listed	
Product Compliance	RoHS; REACH	
	•	



WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.