

GloTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: UK Plug (Type G), BS1363A, Fused at 10A to IEC320-C13, GT Cable #427: 1.0mmsq / 3 Conductors, 7.1mm OD, H05VV-F, 70 Deg.C, 500V, BLU/BRN/GRN-YW, Approvals: EN 50525-2-11; IEC 60227, 2500mm, GlobTek Black	
	Model No. Power Cord	
	Part No./Ordering No. PZ0800100-2M5BK13H(R)	Rev N

CUSTOMIZED LENGTHS, COLORS, CABLE TYPES, TERMINATIONS/PLUGS/RECEPTACLES AVAILABLE UPON REQUEST. ADDITIONAL PLUG OPTIONS ARE AVAILABLE AT <https://www.globtek.com/connectors/> STANDARD PLUGS AND CONNECTORS CAN BE SEEN ONLINE AT <https://www.globtek.com/connectors/> ACTUAL CONNECTORS, OVERMOLDS, FERRITES MAY VARY SLIGHTLY FROM THE PICTURE BELOW DIMENSIONS ARE IN MM UNLESS SPECIFIED OTHERWISE

In Addition to GlobTek Inc.'s renewed ISO9001:2008 - Quality Management System Certification, GlobTek Inc. is now certified to:

ISO13485:2003 - Medical Devices Quality Management System Certification
ISO14001:2004 - Environmental Management System Certification

ISO Certificates are available online at <https://www.globtek.com/iso-certificates/>
Prop 65 Statement: <https://en.globtek.com/prop-65-statement.pdf>

The acceptance of this specification and use of the product described in this document indicates the acceptance and binding of the customer to Globtek TERMS AND CONDITIONS (attached to the end of this document), which supersede all other agreements, terms, and conditions (<https://en.globtek.com/terms-and-conditions/>).

The purchaser of this product (Customer) agrees that it is their sole responsibility to determine suitability/fitness of the product described in this specification for their application and to take precautions for protection against any hazards attendant to the handling and use of the product.

Footnote:

GlobTek Inc. will not be liable for the safety and performance of these power supplies if unauthorized access and repair occurs. End user should consult applicable UL, CSA or EN standards for proper installation instruction.

Limitation of Use:

GlobTek products are intended for use with commercial, medical, and/or industrial equipment only. GlobTek product are not authorized for use as mission critical components in life support hazardous environment, nuclear or aircraft applications without prior written approval from the CEO of GlobTek Inc.
Contents of this document are subject to change without prior notice.

Customer Approval of Specification:

Please approve, sign and send back to GlobTek so we can complete order processing.
A delay in receipt of this form will delay delivery schedule.

Company Name: _____

Customer P/N: _____

Quote Number: _____

Date: _____

Authorized Representative Name: _____

Authorized Representative Signature: _____

GlobTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: UK Plug (Type G), BS1363A, Fused at 10A to IEC320-C13, GT Cable #427: 1.0mmsq / 3 Conductors, 7.1mm OD, H05VV-F, 70 Deg.C, 500V, BLU/BRN/GRN-YW, Approvals: EN 50525-2-11; IEC 60227, 2500mm, GlobTek Black		
	Model No. Power Cord		
	Part No./Ordering No. PZ0800100-2M5BK13H(R)		Rev N

CUSTOMIZED LENGTHS, COLORS, CABLE TYPES, TERMINATIONS/PLUGS/RECEPTACLES AVAILABLE UPON REQUEST. ADDITIONAL PLUG OPTIONS ARE AVAILABLE AT <https://www.globtek.com/connectors/> STANDARD PLUGS AND CONNECTORS CAN BE SEEN ONLINE AT <https://www.globtek.com/connectors/> ACTUAL CONNECTORS, OVERMOLDS, FERRITES MAY VARY SLIGHTLY FROM THE PICTURE BELOW DIMENSIONS ARE IN MM UNLESS SPECIFIED OTHERWISE

REVISION HISTORY

REV	DESCRIPTION	SUB	DATE	APPROVED
N	Add UKCA and CE marking to the IEC320/C13 connector	bsiep	07/15/2021	QA
M	Update to SF format; add Singapore, Malaysia, Hong Kong, Saudi Arabia, and Gulf States approvals. Connector approval updated from individual EU approvals to ENEC-VDE.	bsiep	10/09/2020	QA
L	UPDATE ASTA LICENSE	jsund	02/02/2012	QA

Cordset Information:

CordsetColor:GlobTek Black


Cord Length (mm):2500

NOTES:

BS 1363A fused @ 10A


GlobTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: UK Plug (Type G), BS1363A, Fused at 10A to IEC320-C13, GT Cable #427: 1.0mmsq / 3 Conductors, 7.1mm OD, H05VV-F, 70 Deg.C, 500V, BLU/BRN/GRN-YW, Approvals: EN 50525-2-11; IEC 60227, 2500mm, GlobTek Black	
	Model No. Power Cord	
	Part No./Ordering No. PZ0800100-2M5BK13H(R)	Rev N

CUSTOMIZED LENGTHS, COLORS, CABLE TYPES, TERMINATIONS/PLUGS/RECEPTACLES AVAILABLE UPON REQUEST. ADDITIONAL PLUG OPTIONS ARE AVAILABLE AT <https://www.globtek.com/connectors/> STANDARD PLUGS AND CONNECTORS CAN BE SEEN ONLINE AT <https://www.globtek.com/connectors/> ACTUAL CONNECTORS, OVERMOLDS, FERRITES MAY VARY SLIGHTLY FROM THE PICTURE BELOW DIMENSIONS ARE IN MM UNLESS SPECIFIED OTHERWISE



GlobTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: UK Plug (Type G), BS1363A, Fused at 10A to IEC320-C13, GT Cable #427: 1.0mmsq / 3 Conductors, 7.1mm OD, H05VV-F, 70 Deg.C, 500V, BLU/BRN/GRN-YW, Approvals: EN 50525-2-11; IEC 60227, 2500mm, GlobTek Black	
	Model No. Power Cord	
	Part No./Ordering No. PZ0800100-2M5BK13H(R)	Rev N

CUSTOMIZED LENGTHS, COLORS, CABLE TYPES, TERMINATIONS/PLUGS/RECEPTACLES AVAILABLE UPON REQUEST. ADDITIONAL PLUG OPTIONS ARE AVAILABLE AT <https://www.globtek.com/connectors/> STANDARD PLUGS AND CONNECTORS CAN BE SEEN ONLINE AT <https://www.globtek.com/connectors/> ACTUAL CONNECTORS, OVERMOLDS, FERRITES MAY VARY SLIGHTLY FROM THE PICTURE BELOW DIMENSIONS ARE IN MM UNLESS SPECIFIED OTHERWISE



GloTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: UK Plug (Type G), BS1363A, Fused at 10A to IEC320-C13, GT Cable #427: 1.0mmsq / 3 Conductors, 7.1mm OD, H05VV-F, 70 Deg.C, 500V, BLU/BRN/GRN-YW, Approvals: EN 50525-2-11; IEC 60227, 2500mm, GlobTek Black	
	Model No. Power Cord	
	Part No./Ordering No. PZ0800100-2M5BK13H(R)	Rev N

CUSTOMIZED LENGTHS, COLORS, CABLE TYPES, TERMINATIONS/PLUGS/RECEPTACLES AVAILABLE UPON REQUEST. ADDITIONAL PLUG OPTIONS ARE AVAILABLE AT <https://www.globtek.com/connectors/> STANDARD PLUGS AND CONNECTORS CAN BE SEEN ONLINE AT <https://www.globtek.com/connectors/> ACTUAL CONNECTORS, OVERMOLDS, FERRITES MAY VARY SLIGHTLY FROM THE PICTURE BELOW DIMENSIONS ARE IN MM UNLESS SPECIFIED OTHERWISE

End A Code:PZ0800 Description:UK Plug (Type G), BS1363A, Fused at 10A Rating (V):250 Rating (A):10.0 Gender:Male Overmolded:Yes	Cable Code:427 Description:GT Cable #427: 1.0mmsq / 3 Conductors, 7.1mm OD, H05VV-F, 70 Deg.C, 500V, BLU/BRN/GRN-YW, Approvals: EN 50525-2-11; IEC 60227 Color:GlobTek Black Wire Gauge(AWG):1.0mmsq Cond:3 Type:H05VV-F Temperature:70° C Amps:10 Volts:500 OD:7.1 ConductorsColors:BLU/BRN/GRN-YW	End B Code:701-VDE-ENEC-CE-UKCA Description:IEC320-C13 Rating (V):250 Rating (A):10.0 Gender:Female Overmolded:Yes
Overall cable rating:250VAC 10A		

GlobTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: UK Plug (Type G), BS1363A, Fused at 10A to IEC320-C13, GT Cable #427: 1.0mmsq / 3 Conductors, 7.1mm OD, H05VV-F, 70 Deg.C, 500V, BLU/BRN/GRN-YW, Approvals: EN 50525-2-11; IEC 60227, 2500mm, GlobTek Black	
	Model No. Power Cord	
	Part No./Ordering No. PZ0800100-2M5BK13H(R)	Rev N

CUSTOMIZED LENGTHS, COLORS, CABLE TYPES, TERMINATIONS/PLUGS/RECEPTACLES AVAILABLE UPON REQUEST. ADDITIONAL PLUG OPTIONS ARE AVAILABLE AT <https://www.globtek.com/connectors/> STANDARD PLUGS AND CONNECTORS CAN BE SEEN ONLINE AT <https://www.globtek.com/connectors/> ACTUAL CONNECTORS, OVERMOLDS, FERRITES MAY VARY SLIGHTLY FROM THE PICTURE BELOW DIMENSIONS ARE IN MM UNLESS SPECIFIED OTHERWISE

Plug Approvals		Cable Approvals	Connector Approvals	
 United Kingdom ASTA Diamond Approval Mark  SAFETY MARK  Hong Kong HK safety mark Saudi Arabia SASO safety mark (file # only -- SASO 2203) Malaysia (File number)  Gulf Conformity mark		 European approvals	 ENEC-VDE  UKCA Certification  CE Certification	
AGENCY ONLINE DOCUMENTS		http://en.globtek.com/cordsets/		
RoHS/RoHS3 Declaration		https://www.globtek.com/pdf/rohs_cert/01t30000002p98nAAA		
REACH Declaration		https://www.globtek.com/pdf/iso_certificates/REACH.pdf		
Conflict Minerals Declaration		https://www.globtek.com/pdf/conflict-minerals.pdf		
Prop 65 Statement		https://en.globtek.com/prop-65-statement.pdf		
CE.UKCA.Cord		https://globtek.secure.force.com/spec/ec_decl_product_model_family_incl_cord?id=01t30000002p98n		
IPXY rating is based on 3rd party testing and customers should check suitability and test system level IPXY rating before ordering.				

PROPRIETARY INFORMATION


PROPRIETARY OF GLOBTEK, INC. ANY REPRODUCTION, DISCLOSURE OR USE OF THIS DRAWING, IN WHOLE OR IN PART, IS HEREBY PROHIBITED EXCEPT AS SPECIFIED IN WRITING BY GLOBTEK, INC. © GlobTek, Inc.
2012 - 2023

quest /09/21/2023 5:04:15 PM

GlobTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: UK Plug (Type G), BS1363A, Fused at 10A to IEC320-C13, GT Cable #427: 1.0mmsq / 3 Conductors, 7.1mm OD, H05VV-F, 70 Deg.C, 500V, BLU/BRN/GRN-YW, Approvals: EN 50525-2-11; IEC 60227, 2500mm, GlobTek Black	
	Model No. Power Cord	
	Part No./Ordering No. PZ0800100-2M5BK13H(R)	Rev N

CUSTOMIZED LENGTHS, COLORS, CABLE TYPES, TERMINATIONS/PLUGS/RECEPTACLES AVAILABLE UPON REQUEST. ADDITIONAL PLUG OPTIONS ARE AVAILABLE AT <https://www.globtek.com/connectors/> STANDARD PLUGS AND CONNECTORS CAN BE SEEN ONLINE AT <https://www.globtek.com/connectors/> ACTUAL CONNECTORS, OVERMOLDS, FERRITES MAY VARY SLIGHTLY FROM THE PICTURE BELOW DIMENSIONS ARE IN MM UNLESS SPECIFIED OTHERWISE

Hanking:200
Description:200 +/- 20mm
Image:



Notes/Modifications/Customizations (notes in this section supersede the values shown in the standard spec):