

Specification Sheet

Part Number: 156-02162



Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.

Controlled flex and angled entry promote easy installation.

Independent rotation allows for adjustable routing orientation.

MOC Clip to MOC Clip Perpendicular, 19 mm, 26 mm Perpendicular, PA66HIRHSUV, Black, 2000/ctn

Article Number 156-02162

Type MOC19FMOC26M180

Color Black (BK)

Quantity Per carton

Product Description The MOC to MOC 180 is a rotatable dual routing clip that keeps two routings secured and separated. One clip is oriented 90 degrees from the other to provide alternative access for bundle attachment. A swivel coupler allows them to rotate independently of each other.

Short Description MOC Clip to MOC Clip Perpendicular, 19 mm, 26 mm Perpendicular, PA66HIRHSUV, Black, 2000/ctn

Global Part Name MOC19FMOC26M180-PA66HIRHSUV-BK

Length L (Imperial)	2.86
Length L (Metric)	72.72
Variant	Clip to Clip Transverse
Bundle Diameter Min (Imperial)	0.67
Bundle Diameter Min (Metric)	17.0
Bundle Diameter Max (Imperial)	0.86
Bundle Diameter Max (Metric)	21.8
Height H (Imperial)	1.36
Height H (Metric)	34.5
Depth D (Imperial)	0.47
Depth D (Metric)	12.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB

Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).