

Specification Sheet

Part Number: T30RA300HS



The AT2060 cable tie system is designed for automatic installation on bundles up to 1.25" and a minimum tensile strength of 30 lbs. Available in reels of 3,000 each or bandoliers of 30 each.

Cable Ties for AT2060, 30lb Tensile Strength, PA66HS, Black, 30/bandolier, 600/pkg

Article Number	103-00003
----------------	-----------

Type	T30RA
------	-------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	Includes AT2060 tool, power supply, power cord, tool cord, and maintenance and operation manual.
---------------------	--

Short Description	Cable Ties for AT2060, 30lb Tensile Strength, PA66HS, Black, 30/bandolier, 600/pkg
-------------------	--

Global Part Name	T30RA-PA66HS-BK
------------------	-----------------

Minimum Tensile Strength (Imperial)	30.0
-------------------------------------	------

Minimum Tensile Strength (Metric)	133.4
Length L (Imperial)	6.0
Length L (Metric)	152.4
Identification Plate Position	none
Reel Diameter (Imperial)	17.7
Reel Diameter (Metric))	450.0
Reel Width (Imperial)	7.197
Reel Width (Metric)	182.8
Voltage Range	27 Volt
Releasable Closure	No
Variant	bandolier
Width W (Imperial)	0.14
Width W (Metric)	3.6
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	1.25
Bundle Diameter Max (Metric)	31.75

Thickness T (Imperial)	0.05
Thickness T (Metric)	1.2
Cycle Time	1.2 seconds
Tension Setting Tools	Adjustable
Power Supply	Electrical
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +275°F (-40°C to +135°C)
Reach Compliant (Article 33)	No
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	600
Package Quantity (Metric)	600

Customs Number	3926909988
----------------	------------

Reel Weight (Imperial)	7
------------------------	---

Reel Weight (Metric)	3.175
----------------------	-------

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)