

Specification Sheet

Part Number: 161-05090



Sheathing allows flexible routing and lead-out of cables.
The inner edges are beveled preventing damage to cables.

Sheathing is reusable and resistant to most chemicals.

Spiralwrap is U.L. Recognized.

Spiralwrap Protective Sheathing, 0.38" Diameter, PE, Black, 500ft/roll

Article Number	161-05090
Type	2.5NFP0H
Color	Black (BK)
Quantity Per	reel
Product Description	HellermannTyton’s Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize. Polyethylene is ideal for general applications that are not affected by ordinary solvents. Ultraviolet resistant black polyethylene is for outdoor use. It has the same qualities as clear polyethylene, but also contains an ultraviolet absorber which permits it to be used in direct sunlight for long periods of time. Available in colors.
Short Description	Spiralwrap Protective Sheathing, 0.38" Diameter, PE, Black, 500ft/roll

Global Part Name	2.5NFP0H-PE-BK
------------------	----------------

Local Order Number 2	161-05090
----------------------	-----------

Length L (Imperial)	500.0
---------------------	-------

Length L (Metric)	152.4
-------------------	-------

Variant	Spiral Binding
---------	----------------

Bundle Diameter Min (Imperial)	0.31
--------------------------------	------

Bundle Diameter Min (Metric)	7.92
------------------------------	------

Bundle Diameter Max (Imperial)	3.0
--------------------------------	-----

Bundle Diameter Max (Metric)	76.2
------------------------------	------

Diameter D (Imperial)	0.375
-----------------------	-------

Diameter D (Metric)	9.53
---------------------	------

Nominal Diameter (Imperial)	0.38
-----------------------------	------

Nominal Diameter (Metric)	9.53
---------------------------	------

Wall Thickness WT (Imperial)	.052
------------------------------	------

Wall Thickness WT (Metric)	1.32
----------------------------	------

Material	Polyethylene (PE)
Material Shortcut	PE
UV Resistant (Yes/No)	No
Operating Temperature	-76°F to +190°F (-60°C to +88°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	1500
Package Quantity (Metric)	457.2
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).