




RoHS



P.C.B Layout(Pattern side) CONNECTOR FRONT EDGE

规格说明:Specifications

电气特性:Electrical

- 1.额定电流:Current Rating
PIN1&PIN4(Vbus&Corresponding ground PIN)
1.8A MAX Other PINS 0.25A min.
- 2.额定电压:Voltage Rating
30V DC
- 3.接触阻抗:Contact Resistance
PIN1&PIN4:30mΩ MAX. Other PINS: 50mΩ Max
- 4.耐电压:Dielectric Withstanding Voitage
AC 500V/1MINUTE.
- 5.绝缘阻抗:Insulation Resistance
1000MEGA Ohms Min

物理性能:Mechanical

- 1.插拔力:Connector Mate and Unmate Force
Insertion force:35N(3.57kgf)MAX
Extraction force:10~35N(1.02~3.57kgf)Min

端子保持力:Terminal Retention

1.0kgf(MIN)

耐久性:Durability

3000cycles.EXTRACTLON FORCE:
10~35N(1.02~3.57kgf)

◎	Terminal		1	Brass	Ag plating
◎	Shell		1	Brass	Ni plating
◎	Base		1	PBT	Blue
NO.	Name	Number	Qty	Materil	Remarks

YUANDI® Yuandi Electronics Co.,Ltd

design	date	name	USB CONNECTOR
Review	date	model	USB30-01-T2-BL
Approved	date		

Drawing number: A4

PIN	SIGNAL NAME	PIN	SIGNAL NAME
1	VBUS	7	GND
2	D-	8	SSTX-
3	D+	9	SSTX+
4	GND		
5	SSRX-		
6	SSRX+		

