

Specification Sheet

Part Number: PBM9M4



Push Mounts, when used with standard cable ties, provide a permanent bundling solution below a panel.

The "button" style head is ideal for space constrained areas and is easily inserted through a pre-drilled hole.

Push-Button Cable Tie Mount, 0.25" Hole Dia, 0.12" Max Panel, 0.2" Max Tie Width, PA66, Natural, 1000/pkg

Article Number	151-00233
----------------	-----------

Type	PBM
------	-----

Color	Natural (NA)
-------	--------------

Quantity Per	bag
--------------	-----

Product Description	HellermannTyton Push Mounts are used with our standard cable ties and offer a permanent bundling solution for installation below or underneath a panel. Designed for simple installation by pushing the mount through a pre-drilled hole. The low profile "button" style head is suitable in space constrained areas.
---------------------	---

Short Description	Push-Button Cable Tie Mount, 0.25" Hole Dia, 0.12" Max Panel, 0.2" Max Tie Width, PA66, Natural, 1000/pkg
-------------------	---

Global Part Name	PBM-PA66-NA
------------------	-------------

Length L (Metric)	10.7
Width W (Imperial)	0.26
Width W (Metric)	6.6
Cable Ties	T18 - T50
Height H (Imperial)	.40
Height H (Metric)	10.20
Cable Tie Width Max (Imperial)	0.2
Cable Tie Width Max (Metric)	5.0
Panel Thickness Min (Imperial)	0.118
Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	3.0
Panel Thickness Max (Metric)	3.0
Mounting Hole Diameter D (Imperial)	0.25 - 0.29
Mounting Hole Diameter D (Metric)	6.25 - 6.55 mm
Mounting Hole Diameter D Min (Imperial)	0.25
Mounting Hole Diameter D Max (Imperial)	0.29

Mounting Hole Diameter D Max (Metric) 6.55

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability UL 94 V-2

UV Resistant (Yes/No) No

Operating Temperature -40°F to +185°F (-40°C to +85°C)

Reach Compliant (Article 33) No

ROHS Compliant Yes

Certification/Specification UL

UL Recognized (US) Yes

UL Recognized (US and Canada) Yes

Package Quantity (Imperial) 1000

Package Quantity (Metric) 1000

Customs Number 3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)