

VB RJ45 LaR - DB RJ45 Cat.6A PUR 2.0m



Part number	09 48 854 7745 020
Specification	VB RJ45 LaR - DB RJ45 Cat.6A PUR 2.0m
HARTING eCatalogue	https://b2b.harting.com/09488547745020

Image is for illustration purposes only. Please refer to product description.

Identification

Category	System cabling
Series	RJ45
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING VarioBoot RJ45 Preferred directions left/right
Connector 2	HARTING DualBoot RJ45
Type of cable	Copper cable (round)
Description of the cable	Wiring 1:1 Halogen-free Oil resistant

Version

Cable length	2 m
Number of cores	8
Core structure	4x 2x AWG 26/7

Technical characteristics

Data rate 10 Mbit/s 100 Mbit/s 1 Gbit/s 2.5 Gbit/s 5 Gbit/s	Transmission characteristics	Cat. 6 _A Class E _A up to 500 MHz
Data rate 1 Gbit/s 2.5 Gbit/s		
	Data rate	1 Gbit/s



Technical characteristics

Limiting temperature	-30 +75 °C unmoved -5 +50 °C moved
Degree of protection acc. to IEC 60529	IP20

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Yellow
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Specifications	ISO/IEC 11801 IEC 61156-6
UL / CSA	UL 1863 DUXR.E470046

Commercial data

Packaging size	1
Net weight	97 g
Country of origin	Czechia
European customs tariff number	85444290
GTIN	5713140270169
eCl@ss	27060390 Ready-made data cable (unspecified)