

Acces. Special Cable Clamp EMC M20



Image is for illustration purposes only. Please refer to product description.

Part number	19 62 000 5084
Specification	Acces. Special Cable Clamp EMC M20
HARTING eCatalogue	https://b2b.harting.com/19620005084

Technical characteristics

Wrench size	22
Limiting temperature	-40 ... +130 °C
Degree of protection acc. to IEC 60529	IP68
Size	M20
Clamping range	9 ... 13 mm
Shielding diameter	6.5 ... 10.5 mm
Width across corners	24.4 mm

Material properties

Material (cable glands)	Metal
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
California Proposition 65 substances	Nickel
California Proposition 65 substances	Naphthalene



Pushing Performance
Since 1945

Commercial data

Packaging size	10
Net weight	32 g
Country of origin	Germany
European customs tariff number	84849000
GTIN	5713140132207
eCl@ss	27140803 Cable gland EMC (electrical installation)