

Specification Sheet

Part Number: 553-60006



Halogen free, for low smoke propagation, density and toxicity.

50 mm, 25 mm and 16 mm pre-cut marker options as standard, for ability to get multiple labels out of one tag.

Delivery in convenient storage boxes for protection.

ShrinkTrak Labels, 2-Sided, Unslit, Halogen Free, 1.97" x 1.26", Polyolefin, White, 1500/pkg

Article Number

553-60006

Type

TLFX190DS-1x50WH

Color

White (WH)

Quantity Per

carton

Product Description

ShrinkTrak DS is a halogen-free, double-sided heat shrinkable marker with a 2:1 shrink ratio. HellermannTyton's unique ladder-style design assists in removing markers off the carrier. The side slits have been designed to ensure the wire entry gap is as large as possible while remaining on the carrier strip, enabling the user to quickly insert wire and cable into the marker. For a complete labeling solution, ShrinkTrak DS can be printed using HellermannTyton's TagPrint® Pro professional label creation software and thermal transfer printers. For double-sided printing, HellermannTyton's TrakMark DS double-sided printer produces excellent results. Choose among multiple ribbon types to create a permanent print that resists most solvents when shrunk and applied.

Short Description	ShrinkTrak Labels, 2-Sided, Unslit, Halogen Free, 1.97" x 1.26", Polyolefin, White, 1500/pkg
Global Part Name	TLFX190DS-1x50WH-PO-X-WH
Fixation Method	Suspend
Variant	Roller form
Width W (Imperial)	2.0
Width W (Metric)	50.0
Thickness T (Imperial)	.0130
Thickness T (Metric)	.29
Height H (Imperial)	1.25
Height H (Metric)	32.0
Width of Liner (Metric)	88.9
Width of Liner (Imperial)	3.50
Outside Diameter Max (Imperial)	0.75
Outside Diameter Max (Metric)	19.0
Wall Thickness WT (Imperial)	0.030
Wall Thickness WT (Metric)	0.775

Material	Polyolefin, cross-linked (PO-X)
Material Shortcut	PO-X
US MIL SPEC	MIL-STD-202J SAE AS5942 3.4.1
Flammability	UL 224
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-67°F to +221°F (-55°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	ASTM E 162 ASTM E 662 ASTM 1354 NFPA 130 compliant EN [45545-2]
Package Quantity (Imperial)	1500
Package Quantity (Metric)	1500
Customs Number	3917320000

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)