

Specification Sheet

Part Number: 156-01690



Bundle can rotate to any orientation, allowing routing in any direction regardless of mounting point.

Clip is reusable, making relocation or adjustments simple.

All-in-one bundling and mounting solution reduces costs.

LOC Locking Clamp, 15–19 mm, with T50SMVC Swivel Tie, PA66HIRHSUV, Black, 1000/ctn

Article Number	156-01690
----------------	-----------

Type	T50SMVCLOC15-19
------	-----------------

Color	Black (BK)
-------	------------

Quantity Per	carton
--------------	--------

Product Description	HellermannTyton's 1-Piece Cable Tie with Pipe Clip secures cables to tubular frame rails. The cable tie bundles wires, cables or tubes, and the C-clip snaps onto the tubular frame rail. The clip can be removed from the mounting surface and reinstalled without additional fasteners.
---------------------	---

Short Description	LOC Locking Clamp, 15–19 mm, with T50SMVC Swivel Tie, PA66HIRHSUV, Black, 1000/ctn
-------------------	--

Global Part Name	T50SMVCLOC15-19-PA66HIRHSUV-BK
------------------	--------------------------------

Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	225.0
Length L (Imperial)	8.3
Length L (Metric)	210.0
Fixation Method	Omega Clips
Identification Plate Position	none
Width W (Imperial)	0.47
Width W (Metric)	12.0
Bundle Diameter Min (Imperial)	0.59
Bundle Diameter Min (Metric)	15.0
Bundle Diameter Max (Imperial)	0.75
Bundle Diameter Max (Metric)	19.0
Height H (Imperial)	1.31
Height H (Metric)	33.4
Depth D (Imperial)	0.47
Depth D (Metric)	12.0

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Material Cable Tie	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach

to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)