

SAC-3P-M 8MS/ 1,5-280/M 8FS BK - Sensor/actuator cable



1400343

<https://www.phoenixcontact.com/us/products/1400343>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position halogen-free, Plug straight M8, coding: A, on Socket straight M8, cable length: 1.5 m

Commercial data

Item number	1400343
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF01
Product key	BF1BBA
GTIN	4046356490382
Weight per piece (including packing)	37.8 g
Weight per piece (excluding packing)	36 g
Customs tariff number	85444290
Country of origin	DE

SAC-3P-M 8MS/ 1,5-280/M 8FS BK - Sensor/actuator cable



1400343

<https://www.phoenixcontact.com/us/products/1400343>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	3
No. of cable outlets	1
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Contact resistance	$\leq 5 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Signaling

Status display	No
Status display present	No

Connector

Connection 1

Type	Plug straight M8
Number of positions	3
Coding type	A
Number of positions	3

Connection 2

Type	Socket straight M8
Number of positions	3
	3


SAC-3P-M 8MS/ 1,5-280/M 8FS BK - Sensor/actuator cable



1400343

<https://www.phoenixcontact.com/us/products/1400343>

Cable/line

Cable length	1.5 m
PUR halogen-free gray [280]	
Dimensional drawing	
Cable weight	18 kg/km
UL AWM Style	20549 / 10493 (80°C/300 V)
Number of positions	3
Shielded	no
Cable type	PUR halogen-free gray [280]
Conductor structure signal line	32x 0.10 mm
AWG signal line	24
Conductor cross section	3x 0.25 mm ²
Wire diameter incl. insulation	1.17 mm ±0.02 mm
External cable diameter	3.6 mm ±0.15 mm
Outer sheath, material	PUR
External sheath, color	gray RAL 7001
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, blue, black
Thickness, insulation	≥ 0.21 mm (Core insulation)
Thickness, outer sheath	approx. 0.5 mm
Overall twist	3 wires, twisted
Length of twist, overall twist	40 mm
Max. conductor resistance	≤ 78 Ω/km (at 20 °C)
Insulation resistance	≥ 100 GΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Smallest bending radius, fixed installation	18 mm
Smallest bending radius, movable installation	36 mm
Max. bending cycles	10000000
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	in accordance with UL 758/1581 FT2 DIN EN 60332-2-2 (20 s)
Resistance to oil	in accordance with DIN EN 60811-2-1 hydrolysis and microbe resistant

SAC-3P-M 8MS/ 1,5-280/M 8FS BK - Sensor/actuator cable



1400343

<https://www.phoenixcontact.com/us/products/1400343>

Other resistance	Highly resistant to acids, alkaline solutions and solvents
	Resistant to salt water
	partly UV-resistant in accordance with DIN EN ISO 4892-2-A
Special properties	Flexible cable conduit capable
	Silicone-free
	Free of substances which would hinder coating with paint or varnish
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-25 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-40 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

SAC-3P-M 8MS/ 1,5-280/M 8FS BK - Sensor/actuator cable



1400343

<https://www.phoenixcontact.com/us/products/1400343>

Drawings

Dimensional drawing



M8 x 1 male plug, straight version

Schematic diagram



Pin assignment M8 socket, 3-pos., view female side


SAC-3P-M 8MS/ 1,5-280/M 8FS BK - Sensor/actuator cable



1400343


<https://www.phoenixcontact.com/us/products/1400343>

Dimensional drawing



Socket M8 x 1, straight

Schematic diagram



Pin assignment M8 plug, 3-pos., view male side

SAC-3P-M 8MS/ 1,5-280/M 8FS BK - Sensor/actuator cable



1400343

<https://www.phoenixcontact.com/us/products/1400343>

Circuit diagram



SAC-3P-M 8MS/ 1,5-280/M 8FS BK - Sensor/actuator cable



1400343

<https://www.phoenixcontact.com/us/products/1400343>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1400343>



UL Listed

Approval ID: FILE E 221474

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	60 V	4 A	-	-



cUL Listed

Approval ID: FILE E 221474

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	60 V	4 A	-	-

cULus Listed

SAC-3P-M 8MS/ 1,5-280/M 8FS BK - Sensor/actuator cable



1400343

<https://www.phoenixcontact.com/us/products/1400343>

Classifications

ECLASS

ECLASS-11.0	27060311
ECLASS-12.0	27060311
ECLASS-13.0	27060311

ETIM

ETIM 8.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-3P-M 8MS/ 1,5-280/M 8FS BK - Sensor/actuator cable



1400343
<https://www.phoenixcontact.com/us/products/1400343>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com