

## Specification Sheet

Part Number: 151-03403



Edge clip applies easily to plastic and metal edges without the need for a mounting hole.

Tape bar provides a convenient surface for securing a bundle using a cable tie or tape.

Edge Clip and Tape Clip, EC17, Panel Thickness 0.04" - 0.12", 1.8" Long, PA66HIRHS, Black, 500/pkg

|                |           |
|----------------|-----------|
| Article Number | 151-03403 |
|----------------|-----------|

|      |      |
|------|------|
| Type | EC17 |
|------|------|

|       |            |
|-------|------------|
| Color | Black (BK) |
|-------|------------|

|              |     |
|--------------|-----|
| Quantity Per | bag |
|--------------|-----|

|                     |                                                                                                                                                                                                                                                                                                                                                                                                             |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Description | HellermannTyton's edge clips are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. These edge clips are molded to a tape bar, which can be secured to cables with cable ties or tape. The clip is easy to secure, and the extraction force is high due to the integrated metal clamp that holds the edge clip in place. |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                   |                                                                                                    |
|-------------------|----------------------------------------------------------------------------------------------------|
| Short Description | Edge Clip and Tape Clip, EC17, Panel Thickness 0.04" - 0.12", 1.8" Long, PA66HIRHS, Black, 500/pkg |
|-------------------|----------------------------------------------------------------------------------------------------|

|                                |                                                                  |
|--------------------------------|------------------------------------------------------------------|
| Global Part Name               | EC17-PA66HIRHS-BK                                                |
| Length L (Imperial)            | 1.8                                                              |
| Length L (Metric)              | 46.5                                                             |
| Fixation Method                | Edge Clips                                                       |
| Width W (Imperial)             | 0.39                                                             |
| Width W (Metric)               | 10.0                                                             |
| Height H (Imperial)            | 0.51                                                             |
| Height H (Metric)              | 13.0                                                             |
| Panel Thickness Min (Imperial) | 0.04                                                             |
| Panel Thickness Max (Imperial) | 0.12                                                             |
| Panel Thickness Min (Metric)   | 1.0                                                              |
| Panel Thickness Max (Metric)   | 3.0                                                              |
| Material                       | Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) |
| Material Shortcut              | PA66HIRHS                                                        |
| Flammability                   | UL 94 HB                                                         |

|                              |                                   |
|------------------------------|-----------------------------------|
| UV Resistant (Yes/No)        | No                                |
| Operating Temperature        | -40°F to +221°F (-40°C to +105°C) |
| Reach Compliant (Article 33) | Yes                               |
| ROHS Compliant               | Yes                               |
| Package Quantity (Imperial)  | 500                               |
| Package Quantity (Metric)    | 500                               |
| Customs Number               | 3926909988                        |

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)