








RoHS



PIN NUMBER	SIGNAL NAME
1	V BUS
2	D-
3	D+
4	GND
5	SSRX-
6	SSRX+
7	GND
8	SSTX-
9	SSRT+
Shell	Shield

规格说明:Specifications
电气特性:Electrical

- 额定电流:Current Rating
PIN1&PIN4(Vbus&Corresponding ground PIN)
1.8A MAX Other PINS 0.25A min.
 - 额定电压:Voltage Rating
30V DC
 - 接触阻抗:Contact Resistance
PIN1&PIN4:30mΩ MAX. Other PINS: 50mΩ Max
 - 耐电压:Dielectric Withstanding Voltage
AC 500V/1MINUTE.
 - 绝缘阻抗:Insulation Resistance
1000MEGA Ohms Min
- 物理性能:Mechanical
- 插拔力:Connector Mate and Unmate Force
Insertion force:35N(3.57kgf)MAX
Extraction force:10-35N(1.02-3.57kgf)Min
- 端子保持力:Terminal Retention
1.0kgf(MIN)
- 耐久性:Durability
3000cycles.EXTRACTLON FORCE:
10-35N(1.02-3.57kgf)



◎	Terminal		9	Brass	Ag plating
Ⓑ	Shell		1	SUS	Ni plating
Ⓐ	Base		1	PBT	Blue
NO.	Name	Number	Qty	Materil	Remarks

YUANDI® Yuandi Electronics Co.,Ltd

design	date	name	USB CONNECTOR
Review	date	model	USB30-06-T3-BL
Approved	date		

Drawing number: 1:1 unit mm gage number A4

modify Review Approved

Tolerance not specified

Proportion

1:1

unit

mm

gage number

A4