



Product: [9904](#)

Lead Wire, #4 Str TC, PVC Ins, AWM 1283 AWM 1015

Request Sample

### Product Description

Low Temp Plastic Lead Wire, 4AWG (133x25) Tinned Copper, PVC Insulation, AWM 1283 AWM 1015 CSA TYPE TEW 600V 105C

### Technical Specifications

#### Product Overview

Suitable Applications:	inter-connection circuits, internal wiring of computer and electronic equipments, internal wiring of appliances, machine tool wire
------------------------	--

#### Physical Characteristics (Overall)

##### Conductor

AWG	Stranding	Material	No. of Conductors
4	133x25	TC - Tinned Copper	1

Conductor Count:	1
------------------	---

##### Insulation

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.392 in	0.063 in

#### Electrical Characteristics

##### Conductor DCR

<b>Nominal Conductor DCR</b>
0.27 Ohm/1000ft

##### Current

Element	Max. Recommended Current [A]
Single Conductor in Free Air @ 30C Ambient	Single conductor in free air @ 30°C: 160 A

##### Voltage

<b>UL Voltage Rating</b>
600 V RMS

#### Temperature Range

Non-UL Temp Rating:	105°C
UL Temp Rating:	105°C

#### Mechanical Characteristics

Bulk Cable Weight:	193 lbs/1000ft
Min. Bend Radius/Minor Axis:	1.57 in

#### Standards

NEC Articles:	Article 310
NEC/(UL) Compliance:	MTW
UL Rating:	600V, 105°C

UL AWM Style Compliance:	AWM 1015, AWM 1283
CSA Rating:	600V, 105°C
CSA Type:	TEW

### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
CA Prop 65:	Yes
MII Order #39 (China RoHS):	Yes

### Flammability, LSOH, Toxicity Testing

UL Flammability:	VW-1
UL voltage rating:	600 V RMS

### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

### Related Part Numbers

#### Variants

Item #	Color	Put-Up Type	Length	UPC
9904 01050	Black	Reel	50 ft	612825260349
9904 010500	Black	Reel	500 ft	612825260356
9904 001500	Brown	Reel	500 ft	612825260301
9904 00250	Red	Reel	50 ft	612825260318
9904 002500	Red	Reel	500 ft	612825260325
9904 00750	Violet	Reel	50 ft	612825260332

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

### History

Update and Revision:	Revision Number: 0.381 Revision Date: 05-05-2023
----------------------	--

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.