


1=WH
2=BN
3=GN
4=YE
5=GY
6=BU
PE=GN/PE

HARTING P/N	Type of cable	Cable length(mm)
21375100701050	PUR	5000 ⁺²⁰⁰ ₋₀
21375100701100	PUR	10000 ^{+4,00} ₋₀
21375100703050	PVC	5000 ⁺²⁰⁰ ₋₀
21375100703100	PVC	10000 ^{+4,00} ₋₀

CONTACTANT CARRIER MATERIAL/COLOR	PA6/BLACK	
MOLDED HEAD MATERIAL/COLOR	TPU/BLACK	
CONTACTS	BRASS/GOLD	
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL	
O-RING MATERIAL	NBR	
RATED CURRENT	8 A	
RATED VOLTAGE	300 V	
OUTER CABLE JACKET MATERIAL/CLLOR	PUR/BLACK	PVC/BLACK
CONDUCTOR INSULATION MATERIAL	PP	
NUMBER OF CONDUCTORS (AWG)	7X18AWG	
OPERATING TEMPERATURE	-20°C — +80°C	
PROTECTION CLASS	IEC IP67	



**All Dimensions
in mm**

Tech. Character.	
------------------	--

Free size tol.

According to production drawing



All rights reserved

Department HCS - CN

Created by
LINI

Inspected by	LIANL
--------------	-------

Standardisation
LIANL

Date	2021-03-15
------	------------

State
Final release

Title	
--------------	--

M17 MA str molded 6+PE PUR/PVC open end, L=xxM

Doc-Key / ECM-Nr.	
/	

Type	
------	--

Number

2137 51 00 7 0X XXX

Rev.	
------	--

ev. **A**

Page
1/1

A	First issue.	Ivy Lin	03/15/21
Rev.	Description	Appr.	Date