

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Panel feed-through, Push-in connection, number of positions: 2+PE, 0.5 mm² ... 2.5 mm², 450 V, 16 A, light grey, external cable diameter: 6 mm ... 9 mm and 8 mm ... 13 mm, assembly thread: M25, Push-in connection, cable length: 1 m

Your advantages

- Convenient: quick and easy assembly without special tools

Commercial data

Item number	1047356
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF51
Product key	BF6IAB
Catalog page	Page 469 (C-2-2019)
GTIN	4055626648507
Weight per piece (including packing)	150.24 g
Weight per piece (excluding packing)	150 g
Customs tariff number	85366990
Country of origin	CN

IPD WD 3P2,5 1,0 M25 GY - Panel feed-through



1047356

<https://www.phoenixcontact.com/us/products/1047356>

Technical data

Product properties

Product type	Panel feed-through
Product family	IPD
Number of positions	3
Connection profile	2+PE
Position marking	L, N, PE
Series	IPD

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Connection data

Connection technology

Connection technology	Push-in connection
Connection system, internal	Single wires
Frequency of connections between conductors of the same cross section	10

Conductor connection

Conductor cross section flexibel	0.5 mm ² ... 2.5 mm ²
Conductor cross section solid	0.5 mm ² ... 2.5 mm ²
Connection cross section AWG	20 ... 14

Electrical properties

Rated surge voltage (III/3)	6 kV
Rated current	16 A
Rated voltage (III/3)	450 V
Nominal voltage U _N	450 V AC
	450 V DC
Nominal current I _N	16 A (observe derating)

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	10
-----------------------------	----

Material specifications

Material	PA
Contact material	Cu
Contact surface material	Ni/Sn

Cable/line

IPD WD 3P2,5 1,0 M25 GY - Panel feed-through



1047356

<https://www.phoenixcontact.com/us/products/1047356>

Cable length	1 m
External cable diameter ()	6 mm ... 9 mm
	8 mm ... 13 mm
Stripping length of the individual wire	10 mm
Position marking	L, N, PE
Single wire, color	brown, blue, green/yellow
Halogen-free	no

Mounting


Mounting type	Front mounting M25
Connection method	Push-in connection

Environmental and real-life conditions


Ambient conditions

Degree of protection	IP66
	IP68 (2 m / 24 h)
	IP69K
Ambient temperature (operation)	-40 °C ... 90 °C (T = 45 °C)
Temperature when conductor connected	-5 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 90 °C


Drawings



Derating diagram for 1.0 mm²



Derating diagram for 1.5 mm²



Derating diagram for 2.5 mm²

IPD WD 3P2,5 1,0 M25 GY - Panel feed-through



1047356

<https://www.phoenixcontact.com/us/products/1047356>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1047356>



VDE Zeichengenehmigung

Approval ID: 40049992

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	450 V	20 A	-	0.5 - 2.5



UL Listed

Approval ID: E468743

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Only rigid conductors	600 V	15 A	-	- 14
multi-stranded with ferrule	600 V	15 A	-	- 14



cUL Listed

Approval ID: E468743

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	600 V	20 A	- 14	-

DNV

Approval ID: TAE00004G2

cULus Listed

IPD WD 3P2,5 1,0 M25 GY - Panel feed-through



1047356

<https://www.phoenixcontact.com/us/products/1047356>

Classifications

ECLASS

ECLASS-11.0	27440602
ECLASS-12.0	27440602
ECLASS-13.0	27440602

ETIM

ETIM 8.0	EC002566
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

IPD WD 3P2,5 1,0 M25 GY - Panel feed-through



1047356

<https://www.phoenixcontact.com/us/products/1047356>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

IPD WD 3P2,5 1,0 M25 GY - Panel feed-through



1047356

<https://www.phoenixcontact.com/us/products/1047356>

Accessories

SEALING PLUG 10X16 RD - Closing cap

1400284

<https://www.phoenixcontact.com/us/products/1400284>

Closing cap, for threads pluggable, color: red



SEALING PLUG 7X16 RD - Closing cap

1400255

<https://www.phoenixcontact.com/us/products/1400255>

Closing cap, color: red



IPD WD 3P2,5 1,0 M25 GY - Panel feed-through



1047356

<https://www.phoenixcontact.com/us/products/1047356>

ZBF 4:UNBEDRUCKT - Zack Marker strip, flat

0808587

<https://www.phoenixcontact.com/us/products/0808587>




Zack Marker strip, flat, Strip, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, PLOTMARK, mounting type: snapped, for terminal block width: 4 mm, lettering field size: 4.2 x 5.2 mm, Number of individual labels: 10

UC-TMF 4 - Marker for terminal blocks

0818166

<https://www.phoenixcontact.com/us/products/0818166>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped, for terminal block width: 4.2 mm, lettering field size: 3.6 x 5.1 mm, Number of individual labels: 120

IPD WD 3P2,5 1,0 M25 GY - Panel feed-through



1047356

<https://www.phoenixcontact.com/us/products/1047356>

UCT-TMF 4 - Marker for terminal blocks

0828742

<https://www.phoenixcontact.com/us/products/0828742>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped, for terminal block width: 4.2 mm, lettering field size: 3.4 x 4.7 mm, Number of individual labels: 90

SZF 1-0,6X3,5 - Screwdriver

1204517

<https://www.phoenixcontact.com/us/products/1204517>



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

IPD WD 3P2,5 1,0 M25 GY - Panel feed-through



1047356

<https://www.phoenixcontact.com/us/products/1047356>

CRIMPFOX CENTRUS 6S - Crimping pliers

1213144

<https://www.phoenixcontact.com/us/products/1213144>



Crimping pliers, for uninsulated and insulated ferrules, DIN 46228 Part 1 and 4, from 0.14 mm² ... 6 mm², also for TWIN ferrules up to 2 x 4 mm², automatic cross section adjustment, lateral insertion, equipped with fall protection

QSS 22 - Socket wrench

1670206

<https://www.phoenixcontact.com/us/products/1670206>



Allen wrench, for loosening and fastening the QUICKON union nut, WAF 22 mm

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com