

Specification Sheet

Part Number: CTT20R9C2



Head design contains clamping rails to provide full circumferential compression around bundles.
Bent tail allows for quick insertion into head.

Clamp Tie, 4" Long, 20lb Tensile Strength, PA66, Natural, 100/pkg

Article Number	112-51919
----------------	-----------

Type	CTT20R
------	--------

Color	Natural (NA)
-------	--------------

Quantity Per	bag
--------------	-----

Product Description	HellermannTyton clamp tie has triangular shaped tabs extending beneath the head for optimal surface contact and complete circumferential compression to 360 degrees. The bent tail design allows quick and simple installations by hand. The clamps are recommended for soft rubber hose applications including fuel, water, and air vacuum lines.
---------------------	--

Short Description	Clamp Tie, 4" Long, 20lb Tensile Strength, PA66, Natural, 100/pkg
-------------------	---

Global Part Name	CTT20R-PA66-NA
------------------	----------------

Minimum Tensile Strength (Imperial)	20.0
Minimum Tensile Strength (Metric)	90.0
Length L (Imperial)	4.0
Length L (Metric)	100
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.1
Width W (Metric)	2.5
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.6
Bundle Diameter Max (Imperial)	0.51
Bundle Diameter Max (Metric)	13.0
Thickness T (Imperial)	0.043
Thickness T (Metric)	1.1

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL ANSI/UL 746B UL ANSI/UL 62275 UL ANSI/UL 1565
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)