



Mechanical Dimensions: Inches [mm]


Tolerances ± 0.012 [0.3] Unless Otherwise Specified

Mounting Hole

**Thickness: 0.2[6.0]max**

Circuit Diagram

3P SPDT (ON)-OFF-(ON)



Electrical Specifications

DC Rating	21A 14V DC
AC Rating	20A 125V AC, 10A 277V AC, 3/4HP 125-250V AC 12(4)A 125/250V AC
Contact Resistance	50m ohm Max
Insulation Resistance	DC 500V 100M ohm Min
Dielectric Strength	AC 1500V 1 minute

Material Specifications

Operation Force	1500gf $\pm$ 300 gf
	1 hex nut assy
	1 knurl nut assy
	1 Internal O-Ring
Operation Temperature	-20°C ~ 85°C

Toggle Switch

TA2-1G-DC-1-O



Rev Date of issue Revision Notes

Designed Approved

B	02-13-2020	Initial Drawing	RC	OF
---	------------	-----------------	----	----