



General Information 基本数据信息

TechniData 技术参数
 Standard 标准: ICE61076-2-101
 Operating Temperatur 工作温度: -25° ~+85°
 Insulation Resistance 绝缘电阻: $\geq 100M\Omega$
 Contact Resistance 接触电阻 $\leq 10\Omega$
 IP Class 防水等级 IP67
 Insertion/withdrawal 插拔次数 >100
 Material Data 材料
 Connector Overmold 外模: PVC/TPU
 Connector Carrier material 连接器胶芯: PA
 Connector material 连接器针: Brass With Gold Plated 铜镀金
 Material for screw connection 螺母材料: Brass with Nickel Plated 铜镀镍
 Seal material 密封圈材料: FKM 橡胶
 Shielding 屏蔽罩: Brass with Nickel Plated 铜镀镍

PIN	View plug side	I (A)	U (AC/DC)	AWG	PIN OUT / WIRE COLOR												GND
					1	2	3	4	5	6	8	9	10	11	12		
03		4A	250	22	棕		蓝	黑									GND
04		4A	250	22	棕	白	蓝	黑									GND
05		4A	60	22	棕	白	蓝	黑	灰								GND
08		2A	30	24	白	棕	绿	黄	灰	粉	蓝	红					GND
12		1.5A	30	26	棕	蓝	白	绿	粉	黄	黑	灰	紫	灰/粉	红/蓝		GND

-		-		上海洲日电子有限公司 Shanghai Zhouri Electronics CO.,LTD			
-		-					
物料编码		-		上海康司玛电子设备进出口有限公司 Shanghai KangSiMa Eletronic Equipment Import and export Co.,LTD			
-		-					
绘图: MAXIA		日期: 20230816		tel:021-51571121		http://www.zhouri.net	
审核: ZHANGMEI		日期: 20230817		fax:021-51571120			
版本编号: ZRLCGY2023-08-01-SX/3				产品名称: M12A-M-NP180° -PB L=2000MM			
第三视角:		单位: mm		比例:		图幅: A4 页次 共 01 第 01	