



General Information 基本数据信息

TechniData 技术参数
 Standard 标准: ICE61076-2-101
 Operating Temperatur 工作温度: -25° ~+85°
 Insulation Resistance 绝缘电阻: $\geq 100M\Omega$
 Contact Resistance 接触电阻 $\leq 10\Omega$
 IP Class 防水等级 IP67
 Insertion/withdrawal 插拔次数 >100
 Material Data 材料
 Connector Overmold 外模: PVC/TPU
 Connector Carrier material 连接器胶芯: PA
 Connector material 连接器针: Brass With Gold Plated 铜镀金
 Material for screw connection 螺母材料: Brass with Nickel Plated 铜镀镍
 Seal material 密封圈材料: FKM 橡胶
 Shielding 屏蔽罩: Brass with Nickel Plated 铜镀镍

| PIN | View plug side | I (A) | U (AC/DC) | AWG | PIN OUT / WIRE COLOR | | | | | | | | | | | |
|-----|----------------|-------|-----------|-----|----------------------|---|---|---|---|---|---|---|----|-----|-----|-----|
| | | | | | 1 | 2 | 3 | 4 | 5 | 6 | 8 | 9 | 10 | 11 | 12 | GND |
| 03 | | 4A | 250 | 22 | 棕 | | 蓝 | 黑 | | | | | | | | |
| 04 | | 4A | 250 | 22 | 棕 | 白 | 蓝 | 黑 | | | | | | | | |
| 05 | | 4A | 60 | 22 | 棕 | 白 | 蓝 | 黑 | 灰 | | | | | | | |
| 08 | | 2A | 30 | 24 | 白 | 棕 | 绿 | 黄 | 灰 | 粉 | 蓝 | 红 | | | | |
| 12 | | 1.5A | 30 | 26 | 棕 | 蓝 | 白 | 绿 | 粉 | 黄 | 黑 | 灰 | 紫 | 灰/粉 | 红/蓝 | |

| | | | | | |
|-----------------------------|----------|-------|----------|---|-------------------------|
| - | | - | | 上海洲日电子有限公司 Shanghai Zhouri Electronics CO.,LTD | |
| - | | - | | 上海康司玛电子设备进出口有限公司 Shanghai KangSiMa Eletronic Equipment import and export Co.,LTD | |
| 物料编码 | | - | | tel:021-51571121 fax:021-51571120 | |
| 绘图: | MAXIA | 日期: | 20230816 | http://www.zhouri.net | |
| 审核: | ZHANGMEI | 日期: | 20230818 | 产品名称: M12A-F-NP90° L=2000MM | |
| 版本编号: ZRLCGY2023-08-01-SX/3 | | 第三视角: | | 单位: mm | 比例: 图幅: A4 页次 共 01 第 01 |