




版次	变更摘要	日期
0	新产品发行	2019/12/25
1	2P/3P卡扣尺寸改小, 避空公头干涉	2021/11/15



技术指标:

1. 温度范围: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
2. 额定电压: 250V AC, DC.
3. 耐电压: 800V AC/minute.
4. 接触电阻: $\leq 20\text{m}\Omega$.
5. 绝缘电阻: $\geq 1000\text{M}\Omega$.
6. 额定电流: 3A AC, DC.

CKT	A	B	C
2	2.0	7.0	2.9
3	4.0	9.0	3.1
4	6.0	11.0	4.3
5	8.0	13.0	6.3
6	10.0	15.0	8.3
7	12.0	17.0	6.3
8	14.0	19.0	8.3
9	16.0	21.0	14.3
10	18.0	23.0	14.3
11	20.0	25.0	14.3
12	22.0	27.0	14.3
13	24.0	29.0	14.3
14	26.0	31.0	14.3
15	28.0	33.0	14.3
16	30.0	35.0	14.3
22	42.0	47.0	14.3



一般公差 (TOLERANCE)
 X: ±.50 .XX ±.10
 .X ±.20 .XXX ±.05
 ANGLES ±1°

兆星精密电子 (深圳) 有限公司

品名 (TITLE)	PHB2.0公头胶壳	制图 (DR)	
料号 (DWG.NO)	ZX-PHB2.0-2-10PJK	校对 (CHKD)	
比例 (SCALE)	1:1	审核 (APPD)	
单位 (UNITS)	mm	张数 (SHEET)	1 OF 1
		SIZE	A4
		REV	A