








ROHS



P.C.B LAYOUT(Top view)



Rating:0.5A 30V DC
Contact Resistance: 30 mΩ Max.
Operating temperature:-20℃~70℃
Operating force:3-20N
Operating Life:5,000cycles



Schematic

③	Copper sleeve	——	1	Brass	Ag Plating	——	
②	Terminal	——	3	Phosphor bronze	Ag Plating	——	
①	Housing	——	1	PA46	Black	——	
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK	
APPROVALS			DATE	HRO韓泰[®] ELECTRONICS CO.,LTD			
DRAWN	LIUCAN	2021.11.19					
CHECKED							
APPROVALS							
				TITLE:	PHONE JACKS		
				PART NO.	PJ-3200A-3A		
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
		10~30	±0.20				
		5~10	±0.15				
		~ 5	±0.10				
		±2°		DRAWING NO.	——	SHEET 1 OF	

							CHECKED				TITLE:	PHONE JACKS	
							APPROVALS				PART NO.	PJ-3200A-3A	
	A		NEW				TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
								10~30	±0.20				
								5~10	±0.15				
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.		~ 5	±0.10	±2'	DRAWING NO.		SHEET 1 OF 1