


**SPECIFICATIONS**

Current Rating:3.0AMP  
 Contact Resistance:10mΩMax  
 Dielectric Strength:Min 1000V RMS  
 Operation Temperature:-40°c to +105°c

Contact Material:Brass  
 Contact Plating:Au Over Ni  
 Insulator Material:Polyester(UL94V-0)  
 Standard: PPS  
 Soldering Temperature: 260°C±5° 5S

**Ordering Information**



			GENERAL TOLERANCE	制图 DRAWING	深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd			
			DIM TOL	审核 CHECK				
			X.X ±0.30	批准 APPROVAL	产品名称 TITLE	2.54 单排 圆直排针 L11.96 (塑高3.0)	版本 REV.	A
			X.XX ±0.20	比例 SCALE	产品料号 PART NO.	XDZ254C-1-N-Z-3-0-XX	单位 UNITS	mm
			X.XXX ±0.10	投影 Projection	材料 MATERIAL		页次 SHEET	1/1
			Angle ±3.0°					
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						