





注：本板禁止转输、复制、编辑、修改、以及用其内容进行交流



NOTES1:

UL Standard

1.

Use group	B	C	D
Rated Current	8A	/	8A
Rated Voltage	300V	/	300V

2. Wire range: 28~16AWG

IEC Standard

1.

Pollution Degree	3	2	2
Overvoltage Category	III	III	II
Rate Impulse Voltage(KV)	2.5KV	2.5KV	2.5KV
Rate Voltage(V)	160V	160V	320V
Rate Current(A)	8A	8A	8A

2. wire range: 0.2~1.5mm²

NOTES2:

- Housing: PA66 (UL94V-0)
- Cover: PA66 (UL94V-0)
- Clamp: Copper alloy (Ni Plated)
- Cage: Brass (Ni Plated)
- Screw: Steel (M2,Zn Plated)

NOTES3:

- Pitch: 3.81mm Poles: 02-24P
- Stripping length: 6-7mm
- Operating temperature: -40℃~+105℃
- RoHS Compliance

How to order

MX15EDGKB - 381 - XXP - XXXX - XX - X - X

产品型号

间距

颜色:

01常规颜色

A-Z其他定制

灰色GY 棕色OE 02-99

蓝色BU 红色RD 定制颜色

黑色BK 透明色:TT

绿色GN 黄色YW

透明色:TT 白色WE

Cu铜方块

2:PS平头十字螺丝

Fe铁方块

Pitch Range In mm	Nominal Dimension Range In mm	
-------------------	-------------------------------	--

Over 6	Over 10	Over 30	Over 60	Over 100	Over 150	Over 150
TO 6	TO 10	TO 30	TO 60	TO 100	TO 150	TO 150
TO 10	TO 24	TO 30	TO 60	TO 100	TO 150	TO 150
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00
±0.30	±0.50	±1.00	±1.30	±2°		

REV

ECN NO.

CONTENT

CHK

DATE

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG.	CHK	DATE	23.06.20	UNITS	MM
CHK		DATE		SCALE	1:1
APP.		DATE		NAME	MX15EDGKB-3.81-XXP



CXI MAIXU ELECTRONICS CO., LTD.

慈溪市迈旭电子有限公司

DWGNO.