



| 孔位 | A | B |
|----|------|------|
| 2 | 0 | 5.4 |
| 4 | 4.2 | 9.6 |
| 6 | 8.4 | 13.8 |
| 8 | 12.6 | 18.0 |
| 10 | 16.8 | 22.2 |
| 12 | 21.0 | 26.4 |
| 14 | 25.2 | 30.6 |
| 16 | 29.4 | 34.8 |
| 18 | 33.6 | 39.0 |
| 20 | 37.8 | 43.2 |
| 22 | 42.0 | 47.4 |
| 24 | 46.2 | 51.6 |

使用温度范围 (Ambient temperature Range): $-25^{\circ}\sim+85^{\circ}$

适用线规 (Applicable Wires): AWG 28#~20#

适用基板厚度 (Applicable PCboard thickness): 1.7mm

额定电压 (Voltage rating): 300V AC,DC

额定电流 (Current rating): 4A

接触电阻 (Contact Resistance): $<0.015\Omega$

绝缘电阻 (Insulation Resistance): $\geq 1000M\Omega$

耐压 (Withstand Voltage): 1000V/min

材料 (Material)

1. 基座:

| | | | | | | |
|----------|---------|--------------|----------------|------------------------|--|------------|
| — | | new | | 2015/5/3 | A | 瀚源 |
| ECN BO. | | DESCRIPTION. | | DATE. | REV. | |
| DESIGNED | CHECKED | APPROVAL | DRAWING NUMBER | SCALT: 1/2 | | SCALE: 3:1 |
| Mikey | Tom | Jerry | PART NAME | 9357WV-2xXXP | UNLESS OTHERWISE SPECIFIED, TOLERANCE: | X. ±0.25 |
| | | | MODEL NAME | 9357WV-2xXXP | | X.x ±0.20 |
| | | | 3RD ANGLE PROJ | HanElectricity Co.,LTD | | X.xx ±0.15 |
| | | | | | ANGULAR | ±3 |
| | | | | | FILE.NO. | |