



PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 7A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 10mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material:Wafer Nylon66,UL94V-0  
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
8672WV-02P	3.96	7.92
8672WV-03P	7.92	11.88
8672WV-04P	11.88	15.84
8672WV-05P	15.84	19.80
8672WV-06P	19.80	23.76
8672WV-07P	23.76	27.72
8672WV-08P	27.72	31.68
8672WV-09P	31.68	35.64
8672WV-10P	35.64	39.60
8672WV-11P	39.60	43.56
8672WV-12P	43.56	47.52
8672WV-15P	55.44	59.40

new		2015/5/3	A	瀚源	
ECN BO.		DESCRIPTION.	DATE.		REV.
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2	SCALE: 3:1
Mikey	Tom	Jerry	PART NAME	8672WV-XXP	UNLESS OTHERWISE SPECIFIED,TOLERANCE: X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAR ±3
			MODEL NAME	8672WV-XXP	
			3RD ANGLE PROJ	HanElectricity Co.,LTD	